

1000VA 750W 120V Line-Interactive Cloud-Connected UPS with Remote Monitoring - 10 NEMA 5-15R Outlets (Surge and Battery Backup), LCD, 5-15P Plug, 2U Rack/Tower

MODEL NUMBER: SMART1000LCDNC



UPS with included remote monitoring software provides 24/7 access and control of any size deployment via mobile app or web browser.

Features

1000VA/750W/120V Battery Backup for Small Network Servers and Network Workstations

The SMART1000LCDNC line-interactive cloud-connected UPS system combines cloud connectivity, remote management and advanced protection features. Its flexible form factor is suitable for desktop or floor placement, under desks or workstations, mounted on a wall or installed in 2U of space in a 2-post or 4-post rack. It's recommended for home, office and retail use, as well as network closets in both local and remote locations.

Easy-to-Use Cloud-Enabled Remote Monitoring Powered by Brightlayer

Eaton's cloud-based remote monitoring app offers convenient setup, control and management of a single UPS or a larger deployment. Scan the QR code on the UPS to download the app to your mobile device. Receive alerts, push configurations, silence alarms or control load banks using a mobile app or web browser. Being able to monitor and access multiple UPS systems from a remote location helps reduce the number of site visits, saving you time and money. The unit's NFC (near-field communication) feature lets you configure network settings instantly from your mobile device.

Allows Time to Back Up Critical Files During a Blackout

During short blackouts, the SMART1000LCDNC switches to battery power to keep connected equipment running. This allows you enough time to save data and complete a safe shutdown in case of a longer outage. Once AC power is restored, the SMART1000LCDNC restarts automatically, regardless of battery charge level, saving you a costly site visit.

NEMA 5-15R Outlets and Controllable Load Banks Protect Connected Components

Ten 5-15R outlets provide battery backup and surge protection for your computer, monitor, security camera, router, network switch, server and other electronic devices. Remote monitoring allows individual control of three switchable load banks that can be powered on/off or cycled remotely, saving you an expensive and time-consuming on-site visit.

Automatic Voltage Regulation (AVR) Corrects Low- and High-Voltage Conditions

AVR protects your equipment from incremental hardware damage, data loss and performance problems caused by brownouts and overvoltages. The SMART1000LCDNC can correct brownouts as low as 97V and overvoltages as high as 145V back to nominal 120V power continuously, all while keeping the battery

Highlights

- Cloud-based dashboard allows 24/7 remote monitoring via browser or mobile app
- Cloud-connected UPS sets up in minutes to start protecting your devices
- Create account with two-factor authentication for an additional layer of security
- NFC technology allows easy configuration of network settings from your mobile device
- Switchable load banks let you shut down or reboot devices using the mobile app
- Restarts automatically when AC power is restored, even when battery level is low or absent

Package Includes

- SMART1000LCDNC 1000VA 750W 120V Line-Interactive Cloud-Connected UPS
- Mounting hardware
- Quick Start Guide

fully charged and ready to take over in case of power failure.

Communications Ports

An RJ45 port for Ethernet connectivity enables use of the cloud-based remote monitoring application. A USB-C port provides direct connection to the command line interface (CLI) for configuration and identification of local network parameters.

Intuitive LCD, Home-Friendly Alarm and Diagnostic LEDs Keep You Informed 24/7

The easy-to-read LCD and two status LEDs allow at-a-glance local monitoring of UPS status, voltage, load level, battery level and other vital information. A solid green LED means the battery is charged, a flashing green indicates it is charging and a solid red indicates fault. The audible alarm indicates power outage, low-battery and fault conditions. It can be silenced via the LCD or the remote monitoring app, which will still respond to silenced alarms.

Easy Preventative Maintenance and Initial Troubleshooting

The SMART100LCDNC's self-test capability and user-replaceable internal battery can extend the life of the UPS and minimize disruption to operations. A resettable circuit breaker on the rear of the UPS helps prevent dangerous system overloads.

Specifications

OVERVIEW	
UPC Code	037332280114
UPS Type	Line-Interactive
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	8.4A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	10A
UPS Input Cord Length (ft.)	5
UPS Input Cord Length (m)	1.5
Recommended Electrical Service	15A 120V
Maximum Input Amps	8
Input Frequency	50/60Hz Auto-sensing
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	5
Input Cord Length (m)	1.52
OUTPUT	
Output Capacity (VA)	1000
Output Capacity (kVA)	1.0
Output Capacity (Watts)	750



Powering Business Worldwide

TRIPP LITE
SERIES

Output Capacity (kW)	0.750
Power Factor	0.75
Nominal Voltage Details	120v nominal output in battery mode
Frequency Compatibility	50 / 60 Hz
Output Voltage Regulation (Line Mode)	120V (-15%/+10%)
Output Voltage Regulation (Battery Mode)	120V (±10%)
Load Management Receptacles	3 BANKS: Load Bank 1: 3 outlets Load Bank 2: 3 outlets Load Bank 3: 4 outlets
Output AC Waveform (AC Mode)	Sine Wave
Output (Watts)	750
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	120V
Output Receptacles	(10) 5-15R
Overload Protection	(LINE MODE) 110%±10%,GOES TO FAULT AFTER 5MIN; 120%±10%,GOES TO FAULT IMMEDIATELY; (BATTERY MODE) 110%±10%,SHUTS DOWN IN 5 SEC; 120%±10%, SHUTS DOWN IMMEDIATELY
Customized Load Management Receptacles	3 Load Banks: Load Bank 1: 3 outlets, Load Bank 2: 3 outlets, Load Bank 3: 4 outlets.
Individually Controllable Load Banks	Yes
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	2 min. (750W)
Runtime Half Load (min.)	7 min. (375W)
Expandable Runtime	No
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Up to 8 hours from 10% to 90%
Battery Access	Battery Access Door
Lithium Batteries	No
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 97 to 145V
Overvoltage Correction	Input voltages between 132V and 145V are reduced by 15%
Undervoltage Correction	Input voltages between 97V and 108V are boosted by 18%
USER INTERFACE, ALERTS & CONTROLS	



Powering Business Worldwide

TRIPP LITE
SERIES

Front Panel LCD Display	Backlighted LCD screen offers detailed UPS status and operational information including Input Voltage, Output Voltage, Estimated Runtime (minutes), Output Load Percentage, Output Load Wattage, Battery Voltage, Graphical 4-Bar Battery Charge level and 4 bar load Level. LCD screen also shows UPS status AC Powered or battery operation, Alarm muted (icon flashing) & Alarm disabled (icon steady on).
Switches	ON/OFF/MODE button provides UPS on/off power control (long-press); MUTE/ENTER allows alarm to be muted (long press), and advances the LCD screen display (short tap)
Alarm Cancel Operation	Press the MUTE/ENTER button during a power failure to silence the alarm; Once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery status; Alarm can be disabled entirely via front panel LCD interface (see manual) and via the remote monitoring application.
LED Indicators	Green and Red LEDs. Solid green shows AC operation, flashing green shows AC operation and battery charging. Red LED indicates a UPS fault.
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	380
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Primary Form Factor	Desktop; Rackmount; Tower
Rack Height	2U
Cooling Method	Fan
Included Mounting Accessories	Included mounting brackets enable installation in 2 and 4 post racks, plus upright tower configurations
Installation Form Factors Supported with Included Accessories	2 post 19 inch rackmount; 2 post front mount; 4 post 19 inch rackmount; Tower
Minimum Required Rack Depth (cm)	33.02
Minimum Required Rack Depth (inches)	13
Primary UPS Depth (mm)	279
Primary UPS Height (mm)	87
Primary UPS Width (mm)	437
Shipping Dimensions (hwd / in.)	7.24 x 14.60 x 20.00
Shipping Weight (kg)	12.20
UPS Housing Material	ABS
UPS Power Module Dimensions (hwd, in.)	3.43 x 17.2 x 11.0
UPS Power Module Weight (kg)	10.70
UPS Power Module Weight (lbs.)	23.6
Unit Dimensions (hwd / in.)	3.430 x 17.200 x 11.000
Unit Dimensions (in.)	3.43 x 17.2 x 11.0
Unit Weight (lbs.)	23.6
Unit Weight (kg)	10.70



Powering Business Worldwide

TRIPP LITE
SERIES

ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0-90% non-condensing
AC Mode BTU / Hr. (Full Load)	40.96
AC Mode Efficiency Rating (100% Load)	98.4
Operating Elevation	9843
Audible Noise	Less than 40 dB, front side 1m
COMMUNICATIONS	
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions through cloud-enabled remote monitoring interface.
Network Management Card Description	Cloud-enabled network management interface powered by Eaton Brightlayer Remote Monitoring Application.
Communications Interface	Included network card; Near Field Communication (NFC); RJ45 Network; USB-B
LINE / BATTERY TRANSFER	
Transfer Time	4 milliseconds (Typical), 10ms (max)
Low Voltage Transfer to Battery Power (Setpoint)	97V
High Voltage Transfer to Battery Power (Setpoint)	145V
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic Voltage Regulation (AVR); Hot swappable batteries; Remote management; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
Cold Start	Cold-start operation supported
APPLICATIONS	
UPS Applications	Retail/Point of Sale; Hospitality; Home/Office Desktop; High-End Desktop/Small Network; Home Network
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA C22.2; NOM (Mexico); UL 1778
Product Compliance	FCC Part 15 Class B (USA); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Product Warranty Period (Puerto Rico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.