

Technical data sheet

Flexible Control and Tray Cable TRAY-ER PVC · Unshielded

LUTZE SILFLEX® N Control Cable PVC For Stationary Applications



Identification

Type SI N TRAY-ER 3×AWG4 GR
Part No. [A3080403](#)

Product version

Datasheet version 00

Use/Application/Properties

Application	• Machine tools, machine and plant construction, VAC technology as well as other uses. • Compliant with NFPA 79 requirements • TC-ER-JP for use with cable trays without conduit, which can reduce installation costs in industrial environments • WTTC – wind turbine tray cable rating for use in wind power generation • In dry, damp and wet rooms
Properties	• Crush impact resistant • Gas/vapor-tight sheath per UL 1277 • Non-wicking fillers • Ecolab certified resistance to common cleaning agents and chemicals used in food and beverage washdown procedures • Sunlight resistant • Flame retardant • "direct burial" for installation in the ground • Talc free and silicone free

Construction

Description	SILFLEX® CONTROL CABLE PVC
Number of conductors/cross-section	3×AWG4
Number of conductors	3
Cross-section, metric	25 mm ²
Cross-section AWG	AWG 4
Jacket material	PVC
Jacket color	grey similar to RAL 7001
Outer Ø	24.4 mm
Outer Ø	0.96 inch
Weight	93.5 kg/100 m

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA
Tel. +1 (704) 504-0222
www.lutze.com • info@lutze.com

Technical data sheet

Flexible Control and Tray Cable TRAY-ER PVC · Unshielded

Weight	628 Lbs/Mft
Cu Index	57.4 kg/100 m
Cu Index	386 Lbs/Mft

Construction Element 1

Element construction	AWG4/03C
Conductor construction	AWG 4 (413/30)
Conductor	AWG conductor CU-wire bare
Conductor category	Fine wire Class K
Conductor marking	black • with white number print • Ground conductor: green/yellow
Conductor insulation	PVC/Nylon THHN – THWN

Overall construction

Jacket characteristics	Oil resistant Silicone free
------------------------	--------------------------------

Technical data

Rated voltage U_N	600 V 90C UL TC-ER-JP 1000 V WTTC 90C 600 V UL MTW 1000 V 105C AWM
Temperature range fixed	-40 °C ... +105 °C
Minimum bending radius fixed	4×cable OD

Technical Data Element 1

Element construction	AWG4/03C
----------------------	----------

Approvals/Standards

Approvals	UL Type MTW or DP-1 Meets NEC 336, 392, 725, 727 Class I and II, Div. 2 and Class I Zone 2 per NEC 501, 502, 505 C(UL) TC and CIC FT4 UL 1277 TC-ER-JP WTTC
UL style	AWM 20886
Conformity	CE RoHS REACH TSCA
Oil resistant according to	Oil Res II

Technical data sheet

Flexible Control and Tray Cable TRAY-ER PVC · Unshielded

General

Note

CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU