

Technical data sheet

Flexible Control and Tray Cable TRAY PVC · Unshielded

LUTZE SILFLEX® N Control Cable PVC For Stationary Applications



Identification

Type SI N TRAY 2×AWG18 GR
Part No. [A3081802](#)

Product version

Datasheet version 00

Use/Application/Properties

- | | |
|-------------|--|
| Application | <ul style="list-style-type: none">• Machine tools, machine and plant construction, VAC technology as well as other uses.• Compliant with NFPA 79 requirements• TC for use with cable trays without conduit, which can reduce installation costs in industrial environments• WTTC – wind turbine tray cable rating for use in wind power generation• PLTC for installation in cable trays• ITC Instrumentation Tray Cable• Dry, damp or wet locations |
| Properties | <ul style="list-style-type: none">• Crush impact resistant• Gas/vapor-tight sheath per UL 1277• Non-wicking fillers• Ecolab certified resistance to common cleaning agents and chemicals used in food and beverage washdown procedures• Sunlight resistant• Flame retardant• "direct burial" for installation in the ground• Talc free and silicone free |

Construction

Description	SILFLEX® CONTROL CABLE PVC
Number of conductors/cross-section	2×AWG18
Number of conductors	2
Cross-section, metric	1 mm ²
Cross-section AWG	AWG 18

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0
www.luetze.de • info@luetze.de

Technical data sheet

Flexible Control and Tray Cable TRAY PVC · Unshielded

Jacket material	PVC
Jacket color	grey similar to RAL 7001
Outer Ø	7 mm
Outer Ø	0.276 inch
Weight	6.8 kg/100 m
Weight	46 Lbs/Mft
Cu-Index	1.8 kg/100 m
Cu-Index	12 Lbs/Mft

Construction Element 1

Element construction	AWG18/02C
Conductor construction	AWG 18 (19/30)
Conductor	AWG conductor CU-wire bare
Conductor category	Fine wire Class K
Conductor marking	black • with white number print
Conductor insulation	PVC/Nylon THHN – THWN

Overall construction

Jacket characteristics	Oil resistant Silicone free
------------------------	--------------------------------

Technical data

Rated voltage U_N	600 V 90C UL TC 1000 V WTTC 90C 600 V UL MTW 1000 V 105C AWM
Temperature range fixed	-40 °C ... +105 °C
Minimum bending radius fixed	4×D

Technical Data Element 1

Element construction	AWG18/02C
----------------------	-----------

Certifications/Standards

Certifications	UL Type MTW or DP-1 Meets NEC 336, 392, 725, 727 Class I and II, Div. 2 and Class I Zone 2 per NEC 501, 502, 505 C(UL) TC and CIC FT4 UL 1277 TC WTTC PLTC ITC
UL style	AWM 20886

Technical data sheet

Flexible Control and Tray Cable TRAY PVC · Unshielded

Conformity	CE RoHS REACH TSCA
Oil resistant according to	Oil Res II

General

Note	CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU
------	--