

## FC to LC 9/125 Adapter for Multi-Function Optical Fiber Cable Tester (M/F)

MODEL NUMBER: **T020-001-LC9**



Converts FC connector on Tripp Lite Multi-Function Optical Fiber Cable Tester to an LC connector. Ideal for cable installers or anyone else working in telecom or LAN environments.

### Description

The T020-001-LC9 FC to LC 9/125 Adapter converts a native FC fiber female port on the T020-001-PSF Multi-Function Optical Fiber Cable Tester to an LC female port for 9/125 singlemode cable testing. "9/125" is clearly labeled on the unit to differentiate the T020-001-LC9 from other adapters. Included dust caps keep the connectors clean when not in use.

### Features

#### Converts Cable Tester's FC Connector to an LC Connector

- Ideal for cable installers or anyone else working in telecom or LAN environments
- Perfect for 9/125 singlemode cable testing
- FC male plug connects to cable tester's FC female jack
- Included dust caps keep connectors clean
- For use with T020-001-PSF Multi-Function Optical Fiber Cable Tester

## Specifications

| OVERVIEW                |              |
|-------------------------|--------------|
| UPC Code                | 037332197634 |
| Technology              | Singlemode   |
| PHYSICAL                |              |
| Color                   | Blue; Silver |
| Clad Diameter (microns) | 125          |
| Core Diameter (microns) | 9            |

### Highlights

- Converts native FC jack to an LC female connector
- FC male plug connects to fiber cable tester's FC female jack
- Perfect for 9/125 singlemode cable testing
- Included dust caps keep connectors clean
- For use with T020-001-PSF Optical Fiber Cable Tester

### System Requirements

- T020-001-PSF Multi-Function Optical Fiber Cable Tester

### Package Includes

- T020-001-LC9 FC to LC 9/125 Adapter



*Powering Business Worldwide*

TRIPP LITE  
SERIES

|                                     |                           |
|-------------------------------------|---------------------------|
| Shipping Dimensions (hwd / in.)     | 9.00 x 7.00 x 0.50        |
| Shipping Dimensions (hwd / cm)      | 22.86 x 17.78 x 1.27      |
| Shipping Weight (lbs.)              | 0.04                      |
| Shipping Weight (kg)                | 0.02                      |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Product Compliance                  | RoHS                      |
| <b>WARRANTY &amp; SUPPORT</b>       |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.