

Height-Adjustable Sit-Stand Workstation, Clamp-On

MODEL NUMBER: **WWSSDC**



Adapt a traditional desk for sit-stand ergonomics without modifying the entire work surface. Clamp this workstation to a flat surface up to 3 in. thick, and adjust the height of your monitor and keyboard.

Description

The WWSSDC Standing Desk-Clamp Workstation allows you to enjoy the benefits of standing for a portion of the day without modifying your entire work surface. Simply clamp the WWSSDC to the edge of a fixed-height desk or table from 1 to 3 inches thick. With a single touch, you can change the height of your monitor and keyboard to improve ergonomics, promote health and increase productivity.

To adjust the height of the WWSSDC, press the lever to raise or lower the pneumatic spring arm. The monitor platform and keyboard tray move together to provide smooth transitions between sitting and standing. Increase tension for heavier loads or decrease it for lighter items. The workstation remains stable at all heights. Maximum weight capacity is 29 pounds.

The WWSSDC base can be adjusted from front to back along the clamp plate in 2-inch increments to compensate for different desk depths. Minimum desk depth is 18.9 inches. Maximum desk depth is 31.5 inches.

Monitor platform is 23.6 x 15.7 inches and adjusts between 8.5 and 22 inches above the work surface. It's sturdy enough to support a dual-arm display mount. Integrated cable management reduces cable clutter. Keyboard tray is an oversized 23.6 x 11 inches to accommodate the largest, most popular models. The tray adjusts from desktop level up to 13.5 inches. In certain installations, the tray can be 3 inches below the work surface. The wrist rest is removable. Plugs are included to fill exposed mounting holes.

Features

One-Touch Height Adjustment for Sit-Stand Ergonomics

- Lever raises or lowers pneumatic arm for smooth height adjustment
- Monitor platform and keyboard tray move together for seamless sit-stand transitions
- Use included hex key to increase or decrease tension according to load
- Maximum weight capacity is 29 lb.

Clamp Mount Requires Minimal Desk Space

- Clamps to a flat fixed-height work surface from 1 to 3 in. thick
- Workstation base adjusts from front to back along the clamp plate in 2 in. increments
- Minimum desk depth is 18.9 in.; maximum desk depth is 31.5 in.
- Clamp depth is 3.35 in.
- Provides stability at all workstation heights

Highlights

- Lever for smooth one-touch height adjustment
- Max. height of monitor platform is 22 in. above work surface
- Max. height of keyboard tray is 13.5 in. above work surface
- Keyboard tray holds the largest, most popular models
- Maximum weight capacity is 29 lb.

Package Includes

- Lift mechanism
- Monitor platform
- Keyboard tray with wrist rest
- Keyboard panel
- Keyboard bracket
- Clamp plate
- Clamp bracket
- Support bracket
- Pressure plate
- (2) M8 x 70.5 screws
- (10) M6 x 8 screws
- (2) M6 x 10 screws
- (10) M6 x 12 screws
- (2) M6 x 15 screws
- (2) Hole plugs
- Large hex key
- Small hex key
- Owner's manual

Monitor Platform

- 23.6 x 15.7 in. for flat-panel display, laptop or display mount
- Adjusts between 8.5 and 22 in. above the work surface
- Integrated cable management reduces cable clutter

Keyboard Tray

- Extra-large 23.6 x 11 in. tray holds the largest, most popular models
- Adjusts up to 13.5 in. above the work surface
- Wrist rest is removable
- Mounting hole plugs included

Specifications

OVERVIEW	
UPC Code	037332196866
Device Compatibility	Monitor/HDTV; Computer; Laptop
PHYSICAL	
Color	Black
Motion	Fixed
Mounting Location	Desk Clamp
Maximum Weight Capacity (lbs.)	29
Maximum Weight Capacity (kg)	13
Number of Displays	1
Shipping Dimensions (hwd / in.)	7.90 x 28.30 x 27.40
Shipping Dimensions (hwd / cm)	20.07 x 71.88 x 69.60
Shipping Weight (lbs.)	42.70
Shipping Weight (kg)	19.37
Unit Dimensions (hwd / in.)	22.200 x 23.600 x 31.400
Unit Dimensions (hwd / cm)	NA
Unit Weight (lbs.)	39.00
Unit Weight (kg)	17.69
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.