

Technical data sheet

TPE Motor cables · static · shielded

LUTZE SILFLEX® M (C) MOTOR TPE

Flexible Motor Cable for Allen-Bradley and other systems



Identification

Type SI M(C)TPE SE(4GAWG12) 0,6/1KV OR
Part No. [A3161204](#)

Product version

Datasheet version 00

Use/Application/Properties

- | | |
|-------------|---|
| Application | <ul style="list-style-type: none">• Shielded motor supply cable to connect power to 3-phase motors. VFD's and Servo Drives• Cable design for harsh industrial environments and operating conditions with high noise levels• Improved insulation design with additional conductor stress relief layer as a power distortion suppressant• Compliant with NFPA 79 requirements• TC-ER for use with cable trays without conduit, which can reduce installation costs in industrial environments• Dry, damp or wet locations |
| Properties | <ul style="list-style-type: none">• Improved Design with conductor stress relief layer helps to prevent premature cable failure and reduces corona effects, increasing reliability and lifetime• Crush impact resistant• Gas/vapor-tight sheath per UL 1277• Very round cable with small Diameter• Specially formulated TPE jacket for superior oil resistance• Largely resistant to mineral and vegetable-based cutting oils• Non-wicking fillers• Sunlight resistant• Flame-retardant• Talc free and silicone free |

Construction

Description SILFLEX® M (C) TPE

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)
www.luetze.de • info@luetze.de

17.04.2023 • Subject to technical modification

Part No. [A3161204](#) • Datasheet version: 00

page 1 of 3



SYSTEMATIC TECHNOLOGY

Technical data sheet

TPE Motor cables · static · shielded

Number of conductors/cross-section	(4×AWG12)
Number of conductors	4
Cross-section, metric	4 mm ²
Cross-section AWG	AWG 12
Jacket material	TPE
Jacket color	orange RAL 2003
Outer Ø	13.1 mm
Outer Ø	0.51 inch
Weight	214 Lbs/Mft
Cu-Index	107 Lbs/Mft

Construction Element 1

Element construction	AWG12/4C
Conductor construction	AWG 12 (65/30)
Conductor	AWG conductor CU-wire bare
Conductor category	fine wire Class K
Conductor marking	brown · black · blue · green/yellow
Conductor insulation	PVC/Nylon

Overall construction

Overall shield	Braid shield tinned copper wires optical cover approx. 85 %
Jacket characteristics	Oil resistant mineral oil-resistant bio-oil-resistant Silicone-free

Technical data

Rated voltage U _N	600 V UL TC 600 V UL MTW 1000 V WTTC 1000 V Flexible Motor Supply 600 V UL AWM 105 °C
Temperature range fixed	-40 °C ... +105 °C
Minimum bending radius fixed	6×D

Technical Data Element 1

Element construction	AWG12/4C
----------------------	----------

Technical data sheet

TPE Motor cables · static · shielded

Certifications/Standards

Certifications	UL Flexible Motor Supply Cable
	UL Type TC-ER
	cULus
	UL AWM
	UL MTW
	WTTC
	Class I and II, Div. 2
	Class 1 Div. 2 per NEC
	Zone 2 per NEC 501, 502, 505
	cUL TC
	CIC FT4
	UL 1277
	CE
	RoHS
Conformity	REACH
Oil resistant according to	TSCA
	Oil Res I
	Oil Res II

General

Note	CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU
------	--