

Technical data sheet

Flexible Control and Tray Cable with Blue Conductors for 24V Applications · Unshielded

LÜTZE SILFLEX® Tray-ER Blue PVC

Bilddatei nicht gefunden.



Identification

Type SI N TRAY-ER Blue 3×AWG14 GR
Part No. [A3251403](#)

Product version

Datasheet version 00

Use/Application/Properties

- Application
- Multi-wire control cables with TC-ER „Exposed Run“ approval
 - Machine tools, machine and plant construction, VAC technology as well as other uses.
 - Compliant with NFPA 79 requirements
 - Blue conductors indicating 24 Volt circuits
 - MTW Machine Tool Wire
 - TC-ER for use with cable trays without conduit, which can reduce installation costs in industrial environments
 - Dry, damp or wet conditions
- Properties
- Specially formulated gray PVC jacket for oil resistance
 - Crush impact resistant
 - Gas/vapor-tight sheath per UL 1277
 - Non-wicking fillers
 - Sunlight resistant
 - Flame-retardant
 - Direct burial
 - Talc free and silicone free

Construction

Description SILFLEX® TRAY-ER BLUE PVC
Number of conductors/cross-section 3×AWG14
Number of conductors 3
Cross-section, metric 2.5 mm²
Cross-section AWG AWG 14
Jacket material PVC
Jacket color grey similar to RAL 7001
Outer Ø 8.9 mm
Outer Ø 0.352 inch

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)
www.luetze.de • info@luetze.de

03.07.2023 • Subject to technical modification

Part No. [A3251403](#) • Datasheet version: 00

page 1 of 2



SYSTEMATIC TECHNOLOGY

Technical data sheet

Flexible Control and Tray Cable with Blue Conductors for 24V Applications · Unshielded

Weight	82 Lbs/Mft
Cu-Index	39 Lbs/Mft

Construction Element 1

Element construction	AWG14/3C
Conductor construction	AWG 14 (41/30)
Conductor	AWG conductor CU-wire bare
Conductor category	fine wire Class K
Conductor marking	blue · with white number print · green/yellow
Conductor insulation	PVC/Nylon THHN – THWN

Overall construction

Jacket characteristics	Oil resistant Silicone-free
------------------------	--------------------------------

Technical data

Rated voltage U_N	600 V TC-ER 90C 600 V UL MTW
Temperature range fixed	-40 °C ... +90 °C
Minimum bending radius fixed	4×D

Technical Data Element 1

Element construction	AWG14/3C
----------------------	----------

Certifications/Standards

Certifications	TC-ER UL Type MTW or DP-1 Meets NEC 336,392 Class I and II, Div. 2 and Class I Zone 2 per NEC 501, 502, 505 cUL TC CIC FT4 UL 1277
Conformity	RoHS REACH TSCA
Oil resistant according to	Oil Res I

General

Note	CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU
------	--
