

Technical data sheet · LÜTZE SILFLEX® Tray-ER TPE with UL/TC-ER/WTTC/MTW/CE Approvals



Flexible Motor Cable · Unshielded

Identification	Type Part-No.	SI N TPE TRAY-ER 4×AWG3/0 SW A3323/004
Use/Application/Properties		
Application	• Multi-conductor cable for tray applications, with exposed run (open wiring) approval • Compliant with NFPA 79 for machine tool wiring • TC-ER for use with cable trays without conduit, which can reduce material and labor costs • Metal cutting equipment, machine tools, machine and plant construction, HVAC technology, assembly and production lines, and other industrial applications • WTTC – wind turbine tray cable rating for use in wind power generation • Dry, damp and wet locations	
Properties	• Flexible design with Nylon for crush impact resistance per UL 1277 and easy installation • Specially formulated TPE jacket for superior oil resistance • Cutting oil resistant – mineral & bio/vegetable based oil *specially tested with plant based cutting oil • Non-wicking fillers • Sunlight resistant • Direct burial • UL Type TC-Exposed Run • Talc free • Silicone free	
Construction		

10.03.2017 – Subject to technical modification

Part-No. A3323/004

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA

Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223

www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park

Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU

Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2

www.lutze.com • sales.gb@lutze.co.uk

Technical data sheet · LÜTZE SILFLEX® Tray-ER TPE with UL/TC-ER/WTTC/MTW/CE Approvals

Description	SILFLEX TRAY-ER TPE
Number of conductors/cross-section	4×3/0
Jacket material	TPE
Jacket color	black RAL 9005
Outer Ø	45.6 mm
Outer Ø	1.794 inches
Weight	2982 Lbs/Mft
Cu-Index	2156 Lbs/Mft

Element 1

Element construction	3/0/4C
Conductor construction	3/0 (1665/30)
Conductor	AWG conductor CU-wire bare
Conductor category	feindrähtig
Conductor marking	black with white number print green/yellow
Conductor insulation	PVC/Nylon THHN – THWN

overall construction

Jacket characteristics	Oil resistant Silicone-free mineral oil-resistant bio-oil-resistant
------------------------	--

Technical data

Rated voltage	600 V TC-ER 90C 600 V MTW 90C 1000 V WTTC 90C 600 V UL AWM 105 °C
Temperature range fixed	-40 °C ... +90 °C
Minimum bending radius fixed	4×D

Element 1

Element construction	3/0/4C
----------------------	--------

Approvals/Standards

10.03.2017 – Subject to technical modification

Part-No. A3323/004

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA

Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223

www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park

Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU

Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2

www.lutze.com • sales.gb@lutze.co.uk



SYSTEMATIC TECHNOLOGY

Technical data sheet · LÜTZE SILFLEX® Tray-ER TPE with UL/TC-ER/WTTC/MTW/CE Approvals

Approvals	TC-ER cURus cULus UL Type MTW or DP-1 WTTC Class 1 Div. 2 per NEC Art. 336, 392, 501 cUL TC CIC FT4 UL 1277 UL 509 BUS Drop pending
Conformity	CE REACH RoHS
Oil resistant according to	Oil Res I Oil Res II

General

Note	CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU
------	--

Logo



10.03.2017 – Subject to technical modification

Part-No. A3323/004

USA: LÜTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA
Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223
www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk



SYSTEMATIC TECHNOLOGY