


Technical data sheet

PUR Network cables · ETHERNET · C-track compatible

LÜTZE SUPERFLEX® ETHERNET (C) PUR

For highest requirements

Cat. 5e, Profinet Type C



Identification

Type	SU ET (C) PUR (2×2×AWG22/7)C Cat5e
Part No.	104303
Profinet Type	Type C

Product version

Datasheet version	00
-------------------	----

Use/Application/Properties

Application	• For wiring of industrial field bus systems with the globally accepted TCP/IP protocol • For continuous flexing use e.g. in c-tracks or free movement in the automation technology, transport and conveyor technology, machine tool manufacture
Properties	• High protection against electromagnetic interferences (EMI) • Silicone free • Flame retardant • Hydrolysis-resistant, microbe-resistant, and rot-resistant • Industrial and salt water resistant • Weathering, ozone and UV resistant (normal lighting conditions) • Excellent coolant and lubricant resistance • Largely resistant to oils, greases, alcohol-free benzines and kerosene • Low adhesion, abrasion-resistant, nick-resistant, tear-resistant • Very good alternating bending strength

Construction

Ethernet Key	S/UTQ
Description	SUPERFLEX® ETHERNET (C) PUR
Number of conductors/cross-section	(2×2×AWG22/7)C
Number of conductors	4
Cross-section, metric	0.34 mm ²

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0
www.luetze.de • info@luetze.de

11.03.2025 • Subject to technical modification

Part No. [104303](#) • Datasheet version: 00

page 1 of 3

Technical data sheet

PUR Network cables · ETHERNET · C-track compatible

Cross-section AWG	AWG 22
Jacket material	PUR
Jacket color	green similar to RAL 6018
Outer Ø	6.5 mm
Outer Ø	0.256 inch
Surface	adhesion-free
Weight	6.5 kg/100 m
Weight	44 Lbs/Mft
Cu-Index	3.2 kg/100 m
Cu-Index	21 Lbs/Mft
Mounting	Fast Connect

Construction Element 1

Element construction	(2×2×AWG22/7)
Conductor construction	AWG 22/7
Conductor	AWG conductor CU-wire tin-plated
Conductor marking standard	ISO IEC 11801
Conductor insulation	Special Polyolefin

Overall construction

Overall stranding	Star quad stranding
Overall shield	Braid shield Tinned copper wires Optical cover approx. 85 %
Jacket characteristics	Flame-retardant Silicone free Halogen free

Technical data

Rated voltage	300 V
Test voltage type	AC 1500 V
Temperature range moving	-30 °C ... +70 °C
Temperature range fixed	-40 °C ... +80 °C
Minimum bending radius moving	12×D
Minimum bending radius fixed	6×D
Category	Cat.5e
Bending cycles	≥3 Mio
Travel distance	≤3.5 m
Speed	5 m/s
Acceleration	10 m/s ²

Technical Data Element 1

Element construction	(2×2×AWG22/7)
Operating capacitance wire-wire	approx.48 pF/m

Technical data sheet

PUR Network cables · ETHERNET · C-track compatible

Loop resistance	≤110 mΩ/m
Impedance	nom.100 Ω

Certifications/Standards

Certifications	CMX cULus
Conformity	CE RoHS REACH TSCA
Burning behavior according to	IEC 60332-1 DIN EN 60332-1-2 VDE 0482 322-1-2 UL 1581 part VW-1 Flame Test UL FT1
Halogen free according to	DIN EN 60754-1 IEC 60754-1

General

Note	CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU
------	--