


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A5	NEW RELEASE	03/DEC/2021	
A6	Correct the misspellings of bubble and length on page 2	06/DEC/2022	
A7	CHANGE CABLE PRINTING	28/JULY/2025	

LENGTH±T



NOTE:

1. TESTING CONDITIONS:

A: INSULATION RESISTANCE: 10MΩ

B: VOLTAGE: DC300V/0.01S

C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω

2. SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°,
DRAIN WIRE SOLDER TO CONNECTOR SHELL


PIN OUT

P1	P2	P1	P2
1 ——— 1	BLACK	9 ——— 9	GREY
2 ——— 2	BROWN	10 ——— 10	WHITE
3 ——— 3	RED	11 ——— 11	PINK
4 ——— 4	ORANGE	12 ——— 12	LIGHT GREEN
5 ——— 5	YELLOW	13 ——— 13	BLACK/WHITE
6 ——— 6	GREEN	14 ——— 14	BROWN/WHITE
7 ——— 7	BLUE	15 ——— 15	RED/WHITE
8 ——— 8	PURPLE	SHELL ———	SHELL DRAIN

P/N CHART

ACD P/N	LENGTH±T	
CS-DSDMDB15MF-001.5	1.5FT±0.8inch	457±20mm
CS-DSDMDB15MF-002.5	2.5FT±1inch	762±25mm
CS-DSDMDB15MF-005	5FT±2inch	1524±51mm
CS-DSDMDB15MF-010	10FT±3inch	3048±76mm
CS-DSDMDB15MF-015	15FT±3inch	4572±76mm
CS-DSDMDB15MF-016	16FT±3inch	4877±76mm
CS-DSDMDB15MF-020	20FT±4inch	6096±102mm
CS-DSDMDB15MF-025	25FT±4inch	7620±102mm
CS-DSDMDB15MF-035	30FT±6inch	10668±152mm
CS-DSDMDB15MF-050	50FT±8inch	15240±203mm



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
		APPROVALS	DATE		
DECIMALS	ANGLES	DRAWN XF	CHECKED HYJ	DELUXE DB15M/F MOLDED	
.X ±X	± X°				
.XX ±XX					
.XXX ±XXX					
THIRD ANGLE PROJECTION 		RESP ENG		SIZE DWG. NO. CS-DSDMDB15MF-XXX	
		MFG ENG			
CAD FILE:				SCALE: N/A	SHEET 1 OF 1
				REV. A7	

NOTES: UNLESS OTHERWISE SPECIFIED