

Technical data sheet

Flexible Control Cable for Stationary Applications · Unshielded

LUTZE SILFLEX® N PVC



Identification

Type	SI N PVC 12GAWG20
Part No.	108354A

Product version

Datasheet version	00
-------------------	----

Use/Application/Properties

Application	• Machine tools, machine and plant construction, VAC technology as well as other uses. • Compliant with NFPA 79, Article 12.9
Properties	• Specially formulated gray PVC jacket for oil resistance • Most flexible design without Nylon for easy stripping and easy installation • Easy routing and bending due to flexibility • Easy strip design especially suited for cable assemblies • Resistance to many oils, coolants and solvents • Non-wicking fillers • Talc free and silicone free

Construction

Description	SILFLEX® N PVC
Number of conductors/cross-section	12×AWG20
Number of conductors	12
Cross-section, metric	0.5 mm ²
Cross-section AWG	AWG 20
Jacket material	PVC
Jacket color	grey similar to RAL 7001
Outer Ø	10.8 mm
Outer Ø	0.424 inch
Weight	103 Lbs/Mft
Cu-Index	38 Lbs/Mft

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)
www.luetze.de • info@luetze.de

03.07.2023 • Subject to technical modification

Part No. [108354A](#) • Datasheet version: 00

page 1 of 2



SYSTEMATIC TECHNOLOGY

Technical data sheet

Flexible Control Cable for Stationary Applications · Unshielded

Construction Element 1

Element construction	AWG20/12C
Conductor construction	AWG 20 (10/30)
Conductor	AWG conductor CU-wire bare
Conductor category	fine wire Class K
Conductor marking	black • with white number print • green/yellow
Conductor insulation	PVC

Overall construction

Jacket characteristics	Flame-retardant Oil resistant mineral oil-resistant coolant-resistant solvent-resistant Silicone-free
------------------------	--

Technical data

Rated voltage U_N	600 V UL AWM 90 °C
Temperature range fixed	-40 °C ... +90 °C
Minimum bending radius fixed	4×D

Technical Data Element 1

Element construction	AWG20/12C
----------------------	-----------

Certifications/Standards

Certifications	cURus AWM I/II A/B FT4
UL style	AWM 2587
Conformity	CE RoHS REACH TSCA
Burning behavior according to	UL VW-1
Oil resistant according to	Oil Res II

General

Note	CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU
------	--