

ITEM	DRAWING	REV	DESCRIPTION	MATERIAL	QTY.	NOTE
3		A1	Support Panel	SPCC	1	Black
2		A1	Back Panel	SPCC	1	Black
1		A1	Front Panel	Plastic	1	Black


MAT'L		PRODUCT NO.	C-PPA-48P180C6A
UNITS	mm	PRODUCT NAME	19-inch Cat6A 48-Port Angled 2U Patch Panel with 180 Degree Keystones
SCALE	1:1	DRAWING NO.	
TYPE OF PROJECTION		SHEET 1 OF 1	REV A1

## NOTE:


1. The parts have no obvious indentation, remove burrs, and blunt at acute angles
2. After spraying, the parts are smooth and clean, without appearance defects such as leakage bottom
3. The silk screen must be clear and free of rough edges

1 2 3 4 5 6 7 8


A



B



C



A

B

C

D

E

F

#### ELECTRICAL:

- 1.VOLTAGE RATING: 125 VAC RMS
- 2.CURRENT RATING: 1.5AMP
- 3.CONTACT RESISTANCE: 100 MILLIOHMS MAX @ 500 VDC
- 4.INSULATION RESISTANCE: 1000 MEGOHMS MIN
- 5.INSULATION STRENGTH: 750 VAC RMS 60Hz,1MIN

#### ENVIRONMENTAL:

- 1.STORAGE: -40°C TO +85°C
- 2.OPERATION: 0°C TO 70°C

CONFORM TO TIA/EIA 568BC.2.

#### MECHANICAL:

- 1.HOUSING MATERIAL: PC
- 2.INSERT MATERIAL: PBT
- 3.PCB MATERIAL: FR-4 THICKNESS:1.6mm
- 4.CONTACT MATERIAL: PHOSPHOR BRONZE STAMP PIN T=0.35mm
- 5.IDC CONTACT MATERIAL: PHOSPHOR BRONZE T=50-80u NICKEL PLATING
- 6.WIRE: AWG 22~26

ProLabs

MATERIAL	UNIT	MM	SCALE	1:1
DIMENSIONAL TOLERANCE			DRAWN	
X.X	±0.3			
X.XX	±0.10			
X.XXX	±0.050			
ANGLE	1°			
THIRD ANGLE PROJECTION			CHECK	
			APPROVAL	

1 2 3 4 5 6 7 8