

A

A

B

B

C

C

D

D

E



E

ELECTRICAL:

1.CURRENT RATING: 1.5AMP
 2.CONACT RESISTANCE: 100 MILLIOHMS MAX @ 500 VDC
 3.INSULATION RESISTANCE: 1000 MEGOHMS MIN
 4.INSULATION STRENGTH: 750 VAC RMS 60Hz,1MIN

ENVIRONMENTAL:
 1.STORAGE: -40°C TO +70°C
 2.OPERATION: -20°C TO 60°C
 COMPLY WITH TIA/EIA 568C.2 INTERNATIONAL STANDARD

MECHANICAL:
 1.1DC HOUSING MATERIAL: PBT
 2.PANEL FRAME MATERIAL: SPCC,BLACK OR INDUSTRIAL GREY
 ELECTROSTATIC POWDER COATING
 3.RJ45 JACK LIFE: 750 TIMES MIN
 4.JDC LIFE: 200 TIMES MIN
 5.CONACT MATERIAL: PHOSPHOR BRONZE STAMP PIN T=0.30mm
 6.JDC CONTACT MATERIAL: PHOSPHOR BRONZE NICKEL PLATING
 7.WIRE: AWG 23-24



 ProLabs

MAT'L		PRODUCT NO.	C-PPST-24P110C6
UNITS	mm	PRODUCT NAME	19-inch CAT6 24-Port Straight Patch Panel with 110-Type 1U
SCALE	1:1	DRAWING NO.	
TYPE OF PROJECTION		SHEET 1 OF 1	REV