

Technical data sheet

Cable fittings and accessories



Identification

Type	TOP-T EMC Metal M63×1.5
Part No.	FMM63-CEX

Product version

Datasheet version	00
-------------------	----

Use/Application/Properties

Properties	• Designed for large diameter cables • Two seal inserts for clamping range adjustment • Adapts to different size cable shields • 360° shield termination • Integrated strain relief • Wide sealing and clamping range • Fast and easy to install • manufactured acc. to EN 62444
------------	--

Technical data

Clamping range D	35 mm – 45 mm
Clamping range D	1.378 inch – 1.771 inch
Temperature range	-20 °C ... +100 °C -4 °F ... +212 °F
Intermittent temperature range	-40 °C ... +150 °C -40 °F ... +302 °F
Degree of protection	IP68
Thread form	metric
Thread standard	metric acc. to EN 60423
Thread G	M63×1.5
SW 1	68 mm
SW 2	64 mm

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)
www.luetze.de • info@luetze.de

22.05.2023 • Subject to technical modification

Part No. [FMM63-CEX](#) • Datasheet version: 00

page 1 of 2



SYSTEMATIC TECHNOLOGY

Technical data sheet

Cable fittings and accessories

TL	20 mm
H	45 mm

Construction

Material	Brass nickel-plated
Material seal	CR chloroprene rubber
Material O-ring	NBR
Material clamping insert	PA 6
Surface	nickel-plated

General

PU (units)	1
------------	---

Certifications/Standards

Certifications	cULus
----------------	-------

Notes and Comments

Note	Locknuts sold separately
------	--------------------------

Dimensions

