









XX: No. Of Pin




MSAS-03PMMR-SF7003	26.1	25.0	1.0
MSAS-04PMMR-SF7003	26.1	25.0	1.0
MSAS-05PMMR-SF7003	26.1	25.0	1.0
MSAS-06PMMR-SF7003	25.9	25.2	0.8
MSAS-08PMMR-SF7003	25.9	25.2	0.8
MSAS-17PMMR-SF7003	27.9	27.3	0.6

Item No.	A	B	OD
----------	---	---	----




△Note:

-  * RoHS Compliant
 *  Important dimension
 * Waterproof rate: IP67, mated
 * Connector
 Housing: Thermoplastic, Black
 Pin: Copper alloy, Gold plated
 O-Ring: Rubber, Black
 * Shield: Metal
 * Nut: Metal
 * O-Ring: Rubber, Gray
 * For panel thickness max: 3.0mm
 * For pcb thickness max: 1.6mm
 * The Nut Is Packed Separately In The Bag



Pin Assignment Front View

UNIT : mm




TOLERANCE	
.X	± 0.25
.XX	± 0.1
.XXX	± 0.05
ANGLES	$\pm 1^\circ$

TITLE	N SEN, M12 A -SHLD, SCREW RECEPTACLE, M, M, PCB R	
-------	--	---

SCALE 3:2	SIZE A4	SHEET 1 OF 3
REV. 1	WC-REV. A.3	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Vicky	2025-10-27
DWG NO	CHECKED BY	DATE
MSAS-XXPMMR-SF7003	Ruru	2025-10-27
CUSTOMER	APPROVED BY	DATE
ALTW	Rita	2025-10-27



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

UNIT:mm

TOLERANCE

.X
.XX
.XXX
ANGLES

±0.25
±0.1
±0.05
±1°

TITLE

N SEN, M12 A -SHLD, SCREW
RECEPTACLE, M, M, PCB R

SCALE

3:2

SIZE

A4

SHEET

2

OF

3

REV.

1

WC-REV.

A.3

QC

Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

MSAS-XXPMMR-SF7003

DWG NO

ALTW

DRAWN BY

Vicky

CHECKED BY

Ruru

APPROVED BY

Rita

DATE

2025-10-27

DATE

2025-10-27

DATE

2025-10-27

W10814-03-2001A2

