

# Trooper™ Multiband 5G Cellular and 802.11ac Antennas with High Rejection GPS/GLONASS

Combination Antennas - GNSS, 5G Cellular and Wi-Fi

Trooper Platform



## Description

Rugged multiband LTE MIMO and 802.11ac antennas with high rejection GPS/GLONASS, and compact footprint for high-speed Intelligent Transportation Systems and Industrial IoT applications.

## Technologies

- 5G Cellular
- Wi-Fi
- GPS L1 / GLONASS
- GLONASS

## Features

- No tune, multiband coverage
- Superior out-of-band rejection
- Easy installation and/or replacement
- Weather proof, IP67 housing
- Meets AAR certification requirements



## Trooper™ Multiband 5G Cellular and 802.11ac Antennas with High Rejection GPS/GLONASS Combination Antennas - GNSS, 5G Cellular and Wi-Fi

The Trooper™ antenna platform supports the high speed requirements of complex RF communication systems used for Intelligent Transportation Systems (ITS), and IIoT applications. Its compact footprint makes this antenna platform ideal for installation on surfaces with limited surface space, including leading public safety vehicle rooftops and Industrial IoT (IIoT) cabinet installations. These antennas feature two 5G elements compatible with the world's leading cellular routers supporting 600 MHz to 6 GHz frequencies. In addition, PCTEL's proprietary high-rejection multi-GNSS technology is included for high precision tracking and asset management.

### Features

- No tune, multiband coverage – Dual LTE, 802.11ac Wi-Fi and GPS L1/GLONASS frequencies
- Superior out-of-band rejection via proprietary filtering design
- Metal 3/4-inch stud mount with slotted jam nut provides single cable exit for easy installation and/or replacement
- IP67 compliant design provides maximum protection against water or dust ingress under severe environmental conditions<sup>1</sup>
- UV-resistant black or white housing options complement most vehicular aesthetic requirements
- Meets AAR certification requirements for rail applications

### Certifications



<sup>1</sup> When installed according to PCTEL's installation instructions.

# Trooper™ Multiband 5G Cellular and 802.11ac Antennas with High Rejection GPS/GLONASS

## Combination Antennas - GNSS, 5G Cellular and Wi-Fi

### Standard Configurations

Model	Elements	Cable	Connector <sup>2</sup>	Mount	Housing Color
GLHPDLTE-LTB	LTE (2) GNSS (1)	Two-17 feet Pro-Flex™ Plus 195 (LTE) One-17 feet RG-174/U (GNSS)	SMA Plug (LTE) SMA Plug (GNSS)	1-inch (25.4 mm) hole, 3/4-inch long (19.05 mm) zinc stud mount with jam nut	Black
GLHPDLTE-LTW	LTE (2) GNSS (1)	Two-17 feet Pro-Flex Plus 195 (LTE) One-17 feet RG-174/U (GNSS)	SMA Plug (LTE) SMA Plug (GNSS)	1-inch (25.4 mm) hole, 3/4-inch long (19.05 mm) zinc stud mount with jam nut	White
GLHPDLTEMIMO-LTB	LTE (2) Wi-Fi (2) GNSS (1)	Two-17 feet Pro-Flex Plus 195 (LTE) Two-17 feet Pro-Flex Plus 195 (802.11ac Wi-Fi) One-17 feet RG-174/U (GNSS)	SMA Plug (LTE) Reverse Polarity SMA Plug (Wi-Fi) SMA Plug (GNSS)	1-inch (25.4 mm) hole, 3/4-inch long (19.05 mm) zinc stud mount with jam nut	Black
GLHPDLTEMIMO-LTW	LTE (2) Wi-Fi (2) GNSS (1)	Two-17 feet Pro-Flex Plus 195 (LTE) Two-17 feet Pro-Flex Plus 195 (802.11ac Wi-Fi) One-17 feet RG-174/U (GNSS)	SMA Plug (LTE) Reverse Polarity SMA Plug (Wi-Fi) SMA Plug (GNSS)	1-inch (25.4 mm) hole, 3/4-inch long (19.05 mm) zinc stud mount with jam nut	White
GLHPDM3-LTB	LTE (2) Wi-Fi (3) GNSS (1)	Two-17 feet Pro-Flex Plus 195 (LTE) Three-17 feet Pro-Flex Plus 195 (802.11ac Wi-Fi) One-17 feet RG-174/U (GNSS)	SMA Plug (LTE) Reverse Polarity SMA Plug (Wi-Fi) SMA Plug (GNSS)	1-inch (25.4 mm) hole, 3/4-inch long (19.05 mm) zinc stud mount with jam nut	Black
GLHPDM3-LTW	LTE (2) Wi-Fi (3) GNSS (1)	Two-17 feet Pro-Flex Plus 195 (LTE) Three-17 feet Pro-Flex Plus 195 (802.11ac Wi-Fi) One-17 feet RG-174/U (GNSS)	SMA Plug (LTE) Reverse Polarity SMA Plug (Wi-Fi) SMA Plug (GNSS)	1-inch (25.4 mm) hole, 3/4-inch long (19.05 mm) zinc stud mount with jam nut	White
TRP-2C-1.5FT	LTE (2)	Two-1.5 feet Pro-Flex Plus 195 (LTE)	SMA Plug (LTE)	1-inch (25.4 mm) hole, 3/4-inch long (19.05 mm) zinc stud mount with jam nut	Black
TRP-2C1G-1.5FT	LTE (2) GNSS (1)	Two-1.5 feet Pro-Flex Plus 195 (LTE) One-1.5 feet RG-174/U (GNSS)	SMA Plug (LTE) SMA Plug (GNSS)	1-inch (25.4 mm) hole, 3/4-inch long (19.05 mm) zinc stud mount with jam nut	Black
TRP-2C2W1G-1.5FT	LTE (2) WiFi (2) GNSS (1)	Two-1.5 feet Pro-Flex Plus 195 (LTE) Two-1.5 feet Pro-Flex Plus 195 (802.11ac WiFi) One-1.5 feet RG-174/U (GNSS)	SMA Plug (LTE) Reverse Polarity SMA Plug (WiFi) SMA Plug (GNSS)	1-inch (25.4 mm) hole, 3/4-inch long (19.05 mm) zinc stud mount with jam nut	Black
TRP-3W1G-1.5FT	WiFi (3) GNSS (1)	Three-1.5 feet Pro-Flex Plus 195 (802.11ac WiFi) One-17 feet RG-174/U (GNSS)	Reverse Polarity SMA Plug (WiFi) SMA Plug (GNSS)	1-inch (25.4 mm) hole, 3/4-inch long (19.05 mm) zinc stud mount with jam nut	Black
TRP-2W-1.5FT	WiFi (2)	Two-17 feet Pro-Flex Plus 195 (802.11ac WiFi)	Reverse Polarity SMA Plug (WiFi)	1-inch (25.4 mm) hole, 3/4-inch long (19.05 mm) zinc stud mount with jam nut	Black
TRP-2C2W-1.5FT	LTE (2) WiFi (2)	Two-1.5 feet Pro-Flex Plus 195 (LTE) Two-1.5 feet Pro-Flex Plus 195 (802.11ac WiFi)	SMA Plug (LTE) Reverse Polarity SMA Plug (WiFi)	1-inch (25.4 mm) hole, 3/4-inch long (19.05 mm) zinc stud mount with jam nut	Black

# Trooper™ Multiband 5G Cellular and 802.11ac Antennas with High Rejection GPS/GLONASS

## Combination Antennas - GNSS, 5G Cellular and Wi-Fi

### Electrical Specifications – RF Antennas

F1 (MHz)	F2 (MHz)	SWR <sup>3</sup>	Max	Gain (dB) <sup>3</sup>		Efficiency <sup>3</sup>			Nominal Polarization	Nominal Impedance	Maximum Power
				Typical	Range (±)	Avg	Range (±)				
<b>LTE Primary Port 1 &amp; 2</b>											
617	698	2.2	4.0	2.2	1.8	54%	19%	Linear	50 ohms	50 watts	
698	802	1.4	5.0	4.0	0.9	68%	5%				
824	960	2.7	5.5	4.3	1.2	61%	5%				
1710	2200	1.7	6.5	5.5	0.9	78%	3%				
2300	2690	1.6	8.8	6.8	1.9	78%	4%				
3400	3800	1.9	6.8	6.1	0.7	73%	3%				
5150	5950	2.2	10.1	8.6	1.5	81%	13%				
<b>Wi-Fi Port 3</b>											
2400	2500	1.2	9.4	9.0	0.4	81%	3%	Linear	50 ohms	50 watts	
4900	5900	1.4	9.4	8.9	0.5	70%	12%				

### Minimum Isolation (dB)<sup>3</sup>

	LTE Primary (1 & 2)		Wi-Fi (3)	
LTE Primary (1 & 2)	690 - 960 MHz	9.0	698 - 960 MHz	20.0
	1.71 - 2.7 GHz	15.0	1.71 - 2.7 GHz	17.0
	3.3 - 5.9 GHz	32.0	3.3 - 5.9 GHz	35.0
Wi-Fi (3)			2.4 - 2.5 GHz	21.0
			4.9 - 5.9 GHz	27.0

### Electrical Specifications – GNSS Antenna

Frequency Range	1565 - 1608 MHz
Amplifier Gain	@ 3.0 VDC: 26 dB (typical)
Output VSWR	2.0:1 (maximum)
DC Current	25 mA (typical)
DC Voltage	2.8 - 6.0 V (operating) ≤ 12.0 V (survivability)
Noise Figure	< 2.0 dB (typical)
Out-of-Band Rejection	f <sub>0</sub> = 1586 MHz / f <sub>0</sub> ± 50 MHz: ≥ 60 dBc / f <sub>0</sub> ± 60 MHz: ≥ 70 dBc
Nominal Gain	3 dBiC @ 90° -2 dBiC @ 20°
Polarization	Right hand circular
Nominal Impedance	50 ohms

<sup>1</sup> When installed according to PCTEL's installation instructions.

<sup>2</sup> Consult Customer Service for other connector options.

<sup>3</sup> Measurements taken with 3-ft cables on a 2-ft ground plane.

# Trooper™ Multiband 5G Cellular and 802.11ac Antennas with High Rejection GPS/GLONASS

## Combination Antennas - GNSS, 5G Cellular and Wi-Fi

### Mechanical Specifications

#### Physical

Dimensions (W x H)	4.05 W x 3.46 H inches (10.3 x 8.8 cm)
Weight	<b>2-Port Models</b> TRP-2C-1.5FT TRP-2W-1.5FT  <b>3-Port Models</b> GLHPDLTE-LTB GLHPDLTE-LTW TRP-2C1G-1.5FT  <b>4-Port Models</b> TRP-3W1G-1.5FT TRP-2C2W-1.5FT  <b>5-Port Models</b> GLHPDLTEMIMO-LTB GLHPDLTEMIMO-LTW TRP-2C2W1G-1.5FT  <b>6-Port Models</b> GLHPDM3-LTB GLHPDM3-LTW
	1.9 lbs (30.4 oz)
	2.3 lbs (36.8 oz)
	2.6 lbs (1.18 kg)
	2.9 lbs (46.4 oz)
	3.1 lbs (49.6 oz)
Radome Construction	UV-Stable Rugged Thermoplastics
Operating / Storage Temperature	-40°C to +85°C
Gasket Design & Construction	Contour matching, conformable, thermoplastic-elastomer gasket designed to seal between radome and baseplate. Gasket flexes and conforms to contoured surfaces. Baseplate has a 3M® VHB mounting pad for anti-rotation.

## CONTACT US

**For more information about  
this product contact your  
sales representative or visit  
➤ [pctel.com/antenna-products](http://pctel.com/antenna-products)**

### **Solving Complex Wireless Challenges**

PCTEL, an Amphenol company, is a leading global provider of wireless technology solutions, including purpose-built Industrial IoT devices, antenna systems, and test and measurement products. Trusted by our customers for decades, we solve complex wireless challenges to help organizations stay connected, transform, and grow.



**PCTEL, Inc.**

T: +1 630 372 6800 | [pctel.com](http://pctel.com)

Specifications subject to change without notice. PCTEL® and Trooper™ are trademarks or registered trademarks of PCTEL, Inc. 3M® is a registered trademark of 3M. ©2025 PCTEL, Inc. All rights reserved. (January 2025)