

Technical data sheet

Flexible VFD Cable XHHW-2 with UL Approval

LUTZE DRIVEFLEX® XLPE (C) PVC, Shielded for Stationary Applications



Identification

Type DR XLPE (C) PVC (4GAWG16)
Part No. [A1061604](#)

Product version

Datasheet version 00

Use/Application/Properties

- | | |
|-------------|---|
| Application | <ul style="list-style-type: none">• Dual-shielded motor supply cable to connect power to 3-phase-motors, VFDs and servo drives• Cable design for harsh industrial environments and operating conditions with high noise levels• Type XHHW-2 insulation offering smaller ODs for general VFD applications• Thermoset XLPE offering superior overload and short-circuit temperature• Compliant with NFPA 79 requirements• TC-ER-JP for use with cable trays without conduit, which can reduce installation costs in industrial environments• WTTC – wind turbine tray cable rating for use in wind power generation• Dry, damp or wet conditions |
| Properties | <ul style="list-style-type: none">• Flexible XLPE conductors• Reduced cable diameter• High insulation resistance• Low capacitance insulation• Effective dual layer shield for EMC compliance• Specially formulated jacket for oil resistance and easy strip design• Non-wicking fillers• Ecolab certified resistance to common cleaning agents and chemicals used in food and beverage washdown procedures• Crush impact resistant• Gas/vapor-tight sheath per UL 1277• Sunlight resistant• Flame-retardant• Direct burial• Talc free and silicone free |

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)
www.luetze.de • info@luetze.de

13.07.2023 • Subject to technical modification

Part No. [A1061604](#) • Datasheet version: 00

page 1 of 3



SYSTEMATIC TECHNOLOGY

Technical data sheet

Flexible VFD Cable XHHW-2 with UL Approval

Construction

Description	DRIVEFLEX® XLPE (C) PVC
Number of conductors/cross-section	(4×AWG16)
Number of conductors	4
Cross-section, metric	1.5 mm²
Cross-section AWG	AWG 16
Jacket material	PVC
Jacket color	black similar to RAL 9005
Outer Ø	10.8 mm
Outer Ø	0.425 inch
Weight	124 Lbs/Mft
Cu-Index	54 Lbs/Mft

Construction Element 1

Element construction	26/30
Conductor	AWG conductor CU-wire tin-plated
Conductor category	fine wire Class K
Conductor marking	black • with white number print • green/yellow
Conductor insulation	XLPE XHHW-2 Wet/Dry

Overall construction

Drain wire	CU-wire tin-plated
Overall shield	Foil shield Braid shield tinned copper wires optical cover approx. 80 %
Jacket characteristics	Oil resistant Silicone-free

Technical data

Rated voltage U _N	600 V 90C UL TC-ER-JP 1000 V Flexible VFD servo cable Cable, 1000 V 105C AWM 1000 V WTTC
Temperature range fixed	-40 °C ... +105 °C
Bending radius	6×D

Technical Data Element 1

Element construction	26/30
----------------------	-------

Technical data sheet

Flexible VFD Cable XHHW-2 with UL Approval

Certifications/Standards

Certifications	UL Flexible Motor Supply Cable Flexible VFD Servo Cable cULus TC-ER-JP UL DP-1 Meets NEC 336,392 Class I and II, Div. 2 and Class I Zone 2 per NEC 501, 502, 505 cUL TC CIC FT4 UL 1277 cURus
UL style	AWM 20886
Conformity	CE RoHS REACH TSCA
Oil resistant according to	Oil Res II

General

Note	CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU
------	--