

Technical data sheet

Flexible Control and Tray Cable TRAY-ER PVC · Shielded

LUTZE SILFLEX® N Control Cable (C) PVC For Stationary Applications



Identification

Type SI N (C) PVC TRAY-ER (7×AWG16) GR
Part No. [A3091607](#)

Product version

Datasheet version 00

Use/Application/Properties

- Application
- Dual-shielded multi-conductor cable for tray and control applications
 - Machine tools, machine and plant construction, VAC technology as well as other uses.
 - Compliant with NFPA 79 requirements
 - TC-ER-JP for use with cable trays without conduit, which can reduce installation costs in industrial environments
 - WTTC – wind turbine tray cable rating for use in wind power generation
 - PLTC-ER Power Limited Tray Cable – Exposed Run
 - ITC-ER Instrumentation Tray Cable – Exposed Run
 - Dry, damp or wet locations
- Properties
- Crush impact resistant
 - Gas/vapor-tight sheath per UL 1277
 - Non-wicking fillers
 - Ecolab certified resistance to common cleaning agents and chemicals used in food and beverage washdown procedures
 - Sunlight resistant
 - Flame retardant
 - "direct burial" for installation in the ground
 - Talc free and silicone free

Construction

Description SILFLEX® CONTROL CABLE (C) PVC
Number of conductors/cross-section (7×AWG16)
Number of conductors 7
Cross-section, metric 1.5 mm²

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0
www.luetze.de • info@luetze.de

19.09.2024 • Subject to technical modification

Part No. [A3091607](#) • Datasheet version: 00

page 1 of 3



SYSTEMATIC TECHNOLOGY

Technical data sheet

Flexible Control and Tray Cable TRAY-ER PVC · Shielded

Cross-section AWG	AWG 16
Jacket material	PVC
Jacket color	grey similar to RAL 7001
Outer Ø	10.9 mm
Outer Ø	0.43 inch
Weight	21.5 kg/100 m
Weight	145 Lbs/Mft
Cu-Index	11.2 kg/100 m
Cu-Index	75 Lbs/Mft

Construction Element 1

Element construction	AWG16/7C
Conductor construction	AWG 16 (26/30)
Conductor	AWG conductor CU-wire bare
Conductor category	Fine wire Class K
Conductor marking	black • with white number print • green/yellow
Conductor insulation	PVC/Nylon THHN – THWN

Overall construction

Drain wire	CU-wire tin-plated
Overall shield	Aluminium laminate Foil shield Braid shield Tinned copper wires
Jacket characteristics	Oil resistant Silicone free

Technical data

Rated voltage U_N	600 V 90C UL TC-ER-JP 1000 V WTTC 90C 600 V UL MTW 1000 V 105C AWM
Temperature range fixed	-40 °C ... +105 °C
Minimum bending radius fixed	6×D

Technical Data Element 1

Element construction	AWG16/7C
----------------------	----------

Technical data sheet
Flexible Control and Tray Cable TRAY-ER PVC · Shielded

Certifications/Standards

Certifications	UL Type MTW or DP-1 Meets NEC 336, 392, 725, 727 Class I and II, Div. 2 and Class I Zone 2 per NEC 501, 502, 505 C(UL) TC and CIC FT4 UL 1277 TC-ER-JP WTTC PLTC-ER ITC-ER
UL style	AWM 20886
Conformity	CE RoHS REACH TSCA
Oil resistant according to	Oil Res II

General

Note	CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU
------	--