

Technical data sheet

Flexible Electronic Cable (C) PLTC PVC · Shielded

LUTZE ELECTRONIC (C) PLTC PVC For Stationary Applications



Identification

Type LIY(C)Y (25×AWG20) PLTC
Part No. [A3132025](#)

Product version

Datasheet version 00

Use/Application/Properties

- | | |
|-------------|--|
| Application | <ul style="list-style-type: none">• Multi-conductor industrial grade PLTC electronic cable• Machine tools, machine and plant construction, VAC technology as well as other uses.• Compliant with NFPA 79 requirements• PLTC for installation in cable trays |
| Properties | <ul style="list-style-type: none">• Flexible for easy installation• Easy strip design• Color coded conductors• Specially formulated jacket for oil resistance• Premium durability• Extended temperature range• Sunlight resistant• Gas/vapor-tight sheath per UL 1277• Talc free and silicone free• Ecolab certified resistance to common cleaning agents and chemicals used in food and beverage washdown procedures |

Construction

Description	ELECTRONIC (C) PLTC PVC
Number of conductors/cross-section	25×AWG20
Number of conductors	25
Cross-section, metric	0.5 mm ²
Cross-section AWG	AWG 20
Jacket material	PVC

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)
www.luetze.de • info@luetze.de

13.04.2023 • Subject to technical modification

Part No. [A3132025](#) • Datasheet version: 00

page 1 of 3

Technical data sheet

Flexible Electronic Cable (C) PLTC PVC · Shielded

Jacket color	grey similar to RAL 7001
Outer Ø	12.2 mm
Outer Ø	0.581 inch
Weight	189 Lbs/Mft
Cu-Index	118 Lbs/Mft

Construction Element 1

Element construction	AWG20/25C
Conductor construction	AWG 20 (19/32)
Conductor	AWG conductor CU-wire tin-plated
Conductor category	fine wire
Conductor marking	black · red · white · green · orange · blue · brown · yellow · violet · grey · pink · tan · red/green · red/yellow · red/black · white/black · white/red · white /green · white/yellow · white/blue · white/brown · white/orange · white/grey · white/violet · white/black/red
Conductor insulation	SR-PVC

Overall construction

Drain wire	CU-wire tin-plated
Overall shield	Aluminium laminate Foil shield Braid shield tinned copper wires
Jacket characteristics	Flame-retardant Oil resistant Silicone-free

Technical data

Rated voltage UL	300 V
Temperature range fixed	-40 °C ... +105 °C
Minimum bending radius fixed	4×D

Technical Data Element 1

Element construction	AWG20/25C
----------------------	-----------

Certifications/Standards

Certifications	PLTC UL Type CM AWM II A/B Meets NEC 392,800 Class I and II, Div. 2 Class 1 Div. 2 per NEC 501, 502, 505 (PLTC use only) UL Type 13
UL style	AWM 2464

Technical data sheet

Flexible Electronic Cable (C) PLTC PVC · Shielded

Conformity	CE RoHS REACH TSCA
Burning behavior according to	UL VW-1 UL FT4
Oil resistant according to	Oil Res II

General

Note	CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU
------	--