

Technical data sheet

LUTZE SILFLEX® FBP · Unshielded

Flexible Control Cable for Food and Beverage Processing



Identification

Type SI FBP TPE 4×AWG8
Part No. [A6010804](#)

Product version

Datasheet version 00

Use/Application/Properties

- Application
- Multi-conductor control cable for machine and handling devices in food, beverage and drug processing applications
 - FDA sanctioned jacket material for direct food contact per 21 CFR
 - Compliant with NFPA 79, Article 12.9
 - Suitable for use in food contact zone, splash zone and non-contact zones
- Properties
- FDA compliance tested per 21 CFR 175.300
 - California Proposition 65 (Safe Drinking Water and Toxic Enforcement Act of 1986) compliant
 - REACH 1907/2006/EC compliant
 - RoHS Directive EU 2015/863 compliant
 - Phthalate free jacket
 - Low-capacitance cable
 - Easy stripping and fast installation
 - Ecolab certified resistance to common cleaning agents and chemicals used in food and beverage washdown procedures
 - Easy routing and bending due to flexibility
 - Resistance to most oils and fats
 - Small cable diameters
 - Non-wicking fillers
 - Talc free and silicone free
 - Patented design US-11443871-B2

Construction

Description SILFLEX® FBP TPE
Number of conductors/cross-section 4×AWG8
Number of conductors 4

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)
www.luetze.de • info@luetze.de

07.07.2023 • Subject to technical modification

Part No. [A6010804](#) • Datasheet version: 00

page 1 of 2



SYSTEMATIC TECHNOLOGY

Technical data sheet

LUTZE SILFLEX® FBP · Unshielded

Cross-section, metric	10 mm ²
Cross-section AWG	AWG 8
Jacket material	Thermoplastic Polymer
Jacket color	black similar to RAL 9005
Outer Ø	16.2 mm
Outer Ø	0.636 inch
Weight	311 Lbs/Mft
Cu-Index	31.81 kg/100 m
Cu-Index	214 Lbs/Mft

Construction Element 1

Element construction	4xAWG8
Conductor	AWG conductor CU-wire bare
Conductor category	fine wire Class K
Conductor marking	black • with white number print • green/yellow
Conductor insulation	PP

Technical data

Rated voltage U _N	1000 V 90C UL AWM 20886
Temperature according to UL	90 °C
Temperature range fixed	-40 °C ... +90 °C
Minimum bending radius fixed	4×D

Technical Data Element 1

Element construction	4xAWG8
----------------------	--------

Certifications/Standards

Certifications	21 CFR 175.300 NFPA 79, Artikel 12.9
UL style	AWM 20886
Conformity	CE RoHS REACH TSCA
Burning behavior according to	UL 1581 cable flame

General

Note	CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU
------	--
