





| SIGN                                           | DATE     | DESCRIPTION                                     | APPROVER |
|------------------------------------------------|----------|-------------------------------------------------|----------|
| △                                              | 08/13'12 | structure design is changed                     | Dacheng  |
| △                                              | 08/25'12 | Changed from 250°C±10°/5 Sec to 260°C±5°C/5 Sec | Dacheng  |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |          |                                                 |          |



Material:

- Item ① Terminal lever: Thermoplastic (UL94V-0)
- Item ② Terminal housing: Thermoplastic (UL94V-0)
- Item ③ Spring clamp: Stainless steel
- Item ④ Solder pin: Brass. Tin plated
- Item ⑤ Terminal cover: Thermoplastic (UL94V-0)
- Item ⑥ Terminal pad board : Thermoplastic (UL94V-0)

Electrical:

|       |     |
|-------|-----|
| cULus | VDE |
|-------|-----|

- |                          |                                                                                     |                                                                                     |
|--------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| ● Voltage rating:        | 300 V                                                                               | 450 V                                                                               |
| ● Current rating:        | 11 A                                                                                | 12 A                                                                                |
| ● Wire range:            | 0.5-4mm <sup>2</sup>                                                                |                                                                                     |
| ● Solid wire(AWG):       | 12-20                                                                               |                                                                                     |
| ● Stranded wire(AWG):    | 12-20                                                                               |                                                                                     |
| ● Wire strip length:     | 10-11 mm                                                                            |                                                                                     |
| ● Withstanding Voltage:  | 1.6KV                                                                               | 2.5KV                                                                               |
| ● Operating temperature: | -40°C to +115°C                                                                     |                                                                                     |
| ● Soldering temperature: | 260°C ±5°C/5 Sec                                                                    |                                                                                     |
| ● Safety Approval:       |                                                                                     |                                                                                     |
| ● Critical dimension:    |  |  |

H6 xx 1 0 x 0 xxxx G

No. OF POLES  
02: 2 POLES  
:  
:  
16: 16 POLES

COLOR


- 0: BLACK  
5: GREEN (RAL 6018/T)  
6: BLUE  
8: GREY (RAL 7004/P)

— G: RoHs compliant  
(lead<4%)  
In copper Alloy

1000: "@ " Logo (Standard)  
100A: "ANYTEK" Mark  
Any special item by  
customer request.  
please contact sales  
department.

N = Number of poles  
Dim L =  $N \times 7.5 - 1.0$   
Dim P =  $(N - 1) \times 7.5$

|        | Dim L      | Dim P |
|--------|------------|-------|
| 2-6p   | $\pm 0.15$ |       |
| 7-12p  | $\pm 0.25$ |       |
| 13-16p | $\pm 0.40$ |       |



# ANYTEK

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |                                 |                       |                       |                                                                                       |             |      |           |
|----------|---------------------------------|-----------------------|-----------------------|---------------------------------------------------------------------------------------|-------------|------|-----------|
| TITLE    | H6 7.5mm Series ( Square hloe ) |                       |                       |                                                                                       |             |      |           |
| PART NO. | H6xx10x0xxxxG                   |                       |                       | DWG NO.                                                                               | 8H60501     |      |           |
| APPROVED | CHECKED                         | DESIGNED              | DRAWN                 | CUST NO.                                                                              |             |      | Tolerance |
|          |                                 | Dacheng<br>2012.08.25 | Dacheng<br>2012.08.25 |  | UNIT: mm    | X.   | ±0.50     |
|          |                                 |                       |                       |                                                                                       | SCALE: NONE | X.X  | ±0.30     |
|          |                                 |                       |                       | SHEET: 01/01                                                                          | REV: D      | X.XX | ±0.10     |
|          |                                 |                       |                       |                                                                                       |             | X°   | ±1°       |