



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	
		DATE	APPROVED
A	NEW RELEASE	03/JAN/2007	
A1	Add wiring color	16/JAN/2012	
A2	CHANGE CABLE PRINTING	28/JULY/2025	



CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80° C 300V  
26AWG VW-1 LL84201 CSA AWM I/II A 80° C 300V 26AWG FT1 COPARTNER



- NOTE:
- TESTING CONDITIONS:
    - A: INSULATION RESISTANCE: 10MΩ
    - B: VOLTAGE: DC300V/0.01S
    - C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω
  - SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°, DRAIN WIRE SOLDER TO CONNECTOR SHELL

P/N CHART

ACD P/N	LENGTH±T	
CS-DSDMDB25MM-002.5	2.5FT±1inch	762±25mm
CS-DSDMDB25MM-005	5FT±2inch	1524±51mm
CS-DSDMDB25MM-010	10FT±3inch	3048±76mm
CS-DSDMDB25MM-015	15FT±3inch	4572±76mm
CS-DSDMDB25MM-025	25FT±4inch	7620±102mm
CS-DSDMDB25MM-50	50FT±8inch	15240±203mm
CS-DSDMDB25MM-125	125FT±8inch	38100±300mm

PIN OUT			
P1	P2	P1	P2
1	1	14	14
2	2	15	15
3	3	16	16
4	4	17	17
5	5	18	18
6	6	19	19
7	7	20	20
8	8	21	21
9	9	22	22
10	10	23	23
11	11	24	24
12	12	25	25
13	13	SHELL	SHELL
			DRAIN WIRE



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:

DECIMALS	±.X	ANGLES	± X°
.XX	±.XX		
.XXX	±.XXX		

THIRD ANGLE PROJECTION

CAD FILE:

EAR NO.		Amphenol Cables on Demand	
APPROVALS		20 VALLEY ST. ENDICOTT, NY 13760	
DRAWN	XF	DATE	
CHECKED	HYJ	ASM CBL Deluxe 25PIN D-Sub MM	
RESP ENG		SIZE	A
MFG ENG		DWG. NO.	CS-DSDMDB25MM-XXX
		REV.	A2

SCALE SHEET 1 OF 1

NOTES: UNLESS OTHERWISE SPECIFIED