


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.		DESCRIPTION	DATE	APPROVED
A4		NEW RELEASE	14/MAR/2021	
A5		Correct the misspellings of bubble and length on page 2	06/DEC/2022	
A6		CHANGE CABLE PRINTING	28/JULY/2025	



CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80°C 300V
26AWG VW-1 LL84201 CSA AWM I/II A 80°C 300V 26AWG FT1 COPARTNER

NOTE:

- TESTING CONDITIONS:
A: INSULATION RESISTANCE: 10MΩ
B: VOLTAGE: DC300V/0.01S
C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω
- SHIELDING: METAL CAN SHIELD, DRAIN WIRE SOLDER TO CONNECTOR SHELL

PIN OUT	
P1	P2
1	1 BLACK
2	2 BROWN
3	3 RED
4	4 ORANGE
5	5 YELLOW
6	6 GREEN
7	7 BLUE
8	8 PURPLE
9	9 GREY
SHELL	SHELL DRAIN

P/N CHART

ACD P/N	LENGTH±T	
CS-DSPMDB09MM-001	1FT±1inch	305±25mm
CS-DSPMDB09MM-002.5	2.5FT±1inch	762±25mm
CS-DSPMDB09MM-005	5FT±2inch	1524±51mm
CS-DSPMDB09MM-006	6FT±2inch	1829±51mm
CS-DSPMDB09MM-010	10FT±3inch	3048±76mm
CS-DSPMDB09MM-012	12FT±3inch	3660±76mm
CS-DSPMDB09MM-015	15FT±3inch	4572±76mm
CS-DSPMDB09MM-025	25FT±4inch	7620±102mm
CS-DSPMDB09MM-050	50FT±8inch	15240±203mm
CS-DSPMDB09MM-100	100FT±8inch	30480±203mm



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
DECIMALS	ANGLES	APPROVALS	DATE		
.X ±X ±X°		DRAWN XF		CABLE, DB9M/M DBL SHLD XFT	
.XX ±XX		CHECKED HYJ			
.XXX ±XXX		RESP ENG			
THIRD ANGLE PROJECTION		MFG ENG		SIZE A	DWG. NO. CS-DSPMDB09MM-XXX
CAD FILE:					REV. A6
				SCALE: N/A	SHEET 1 OF 1

NOTES: UNLESS OTHERWISE SPECIFIED