


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A2	NEW RELEASE	25/AUG./2022	
A3	Correct the misspellings of bubble and length on page 2	06/DEC/2022	
A4	CHANGE CABLE PRINTING	28/JULY/2025	



CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80° C 300V
26AWG VW-1 LL84201 CSA AWM I/II A 80° C 300V 26AWG FT1 COPARTNER

- NOTE:
- TESTING CONDITIONS:
 - A: INSULATION RESISTANCE: 10MΩ
 - B: VOLTAGE: DC300V/0.01S
 - C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω
 - SHIELDING: METAL CAN SHIELD, DRAIN WIRE SOLDER TO CONNECTOR SHELL

P/N CHART

ACD P/N	LENGTH±T	
CS-DSPMDB25MF-002.5	2.5FT±1inch	762±25mm
CS-DSPMDB25MF-004	4.0FT±2inch	1219±51mm
CS-DSPMDB25MF-005	5FT±2inch	1524±51mm
CS-DSPMDB25MF-006	6FT±2inch	1829±51mm
CS-DSPMDB25MF-010	10FT±3inch	3048±76mm
CS-DSPMDB25MF-012	12FT±3inch	3658±76mm
CS-DSPMDB25MF-015	15FT±3inch	4572±76mm
CS-DSPMDB25MF-018	18FT±4inch	5486±102mm
CS-DSPMDB25MF-025	25FT±4inch	7620±102mm
CS-DSPMDB25MF-050	50FT±8inch	15240±203mm

PIN OUT			
P1	P2	P1	P2
1	1 BLACK	14	14 BROWN/WHITE
2	2 BROWN	15	15 RED/WHITE
3	3 RED	16	16 ORANGE/WHITE
4	4 ORANGE	17	17 GREEN/WHITE
5	5 YELLOW	18	18 BLUE/WHITE
6	6 GREEN	19	19 PURPLE/WHITE
7	7 BLUE	20	20 RED/BLACK
8	8 PURPLE	21	21 ORANGE/BLACK
9	9 GREY	22	22 YELLOW/BLACK
10	10 WHITE	23	23 GREEN/BLACK
11	11 PINK	24	24 GRAY/BLACK
12	12 LIGHT GREEN	25	25 PINK/BLACK
13	13 BLACK/WHITE	SHELL	SHELL DRAIN



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: DECIMALS .X ±X .XX ±XX .XXX ±XXX ANGLES ±X° THIRD ANGLE PROJECTION CAD FILE:		EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
		APPROVALS DRAWN CHECKED RESP ENG MFG ENG	DATE		
		XF		CABLE, DB25 M/F DBL SHLD	
		HYJ			
				SIZE A	DWG. NO. CS-DSPMDB25MF-XXX
					REV. A4
				SCALE: N/A	SHEET 1 OF 1

NOTES: UNLESS OTHERWISE SPECIFIED