




REV.		DESCRIPTION	DATE	APPROVED
A2		NEW RELEASE	03/DEC/2021	
A3		Correct the misspellings of bubble and length on page 2	06/DEC/2022	
A4		CHANGE CABLE PRINTING	28/JULY/2025	



CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80°C 300V
26AWG VW-1 LL84201 CSA AWM I/II A 80°C 300V 26AWG FT1 COPARTNER



- NOTE:
- TESTING CONDITIONS:
 - A: INSULATION RESISTANCE: 10MΩ
 - B: VOLTAGE: DC300V/0.01S
 - C: CONDUCTOR RESISTANCE 2Ω(<3M), 5Ω(>3M), 8Ω(≥10M)
 - SHIELDING: AL-FOIL TAPE COVER PREMOLD 360°, DRAIN WIRE SOLDER TO CONNECTOR SHELL

PIN OUT	
P1	P2
1	1 BLACK
2	2 BROWN
3	3 RED
4	4 ORANGE
5	5 YELLOW
6	6 GREEN
7	7 BLUE
8	8 PURPLE
9	9 GREY
SHELL	SHELL DRAIN

P/N CHART

ACD P/N	LENGTH±T	
CS-DSSMDB9MF0-002.5	2.5FT±1inch	762±25mm
CS-DSSMDB9MF0-005	5FT±2inch	1524±51mm
CS-DSSMDB9MF0-010	10FT±3inch	3048±76mm
CS-DSSMDB9MF0-025	25FT±4inch	7620±102mm
CS-DSSMDB9MF0-050	50FT±6inch	15240±152mm



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
DECIMALS		APPROVALS	DATE		
.X	±X	DRAWN	XF	Standard 9Pin D-Sub, Molded Male/Female, XFT	
.XX	±XX	CHECKED	HYJ		
.XXX	±XXX	RESP ENG			
THIRD ANGLE PROJECTION		MFG ENG		SIZE	DWG. NO.
				A	CS-DSSMDB9MF0-XXX
CAD FILE:				SCALE: N/A	SHEET 1 OF 1

NOTES: UNLESS OTHERWISE SPECIFIED