





AHSP P/N	LENGTH "A"	ACD P/N	DIAMETER "B"	DESCRIPTION
NBCCDB-C102	2000 MM ±50 MM	CS-SASMINIHD2-002	7.0" ± 1.0"	MINISAS HD TO MINISAS HD 28AWG, 2M
NBCCDB-C103	3000 MM ±75 MM	CS-SASMINIHD2-003	7.0" ± 1.0"	MINISAS HD TO MINISAS HD 28AWG, 3M
NBCCDB-C104	4000 MM ±75 MM	CS-SASMINIHD2-004	7.0" ± 1.0"	MINISAS HD TO MINISAS HD 28AWG, 4M

ZONE	REV.	ECN NUMBER	DESCRIPTION	BY	DATE	APPROVED
	A	RGAO-21010302	NEW RELEASE	R.LI	12/04/2020	F.HONG
	B	RGAO-21020309	ADDED DESCRIPTION COLUMN TO TABLE 1.	N.ZENG	2/4/2021	F.HONG
	C	RGAO-24020102	ADDED NEW LENGTH 4m TO TABLE 1.	N.ZENG	2/4/2024	F.HONG

ITEM No.	DESCRIPTION
1	28 AWG 4PR, BLACK, UL CL2 CSA FT4 75°C, AWM 75°C
2	PLUG, HDMSAS - REFERENCE SFF-8644
3	LABEL, WRAPPED - AHSP P/N & REV, DATE CODE, COUNTRY OF ORIGIN AND SERIAL NUMBER
4	LANYARD, HDMSAS, BLUE, UL 94V-0




BAGGED CABLE ASSY NOT TO SCALE



- THIS DRAWING IS RESERVED FOR AMPHENOL CABLES ON DEMAND (NO CUSTOMER DRAWING)..
- TEST COMPLETED ASSEMBLIES PER ACS-1189. TEST ASSEMBLIES AT 12.00 Gbps AND/OR PER AMPHENOL IOPS-4001 SPEC.
- UL LABEL MUST BE ON SHIPPING CARTON PER SUBJECT 764 OF THE UL COMPONENT WIRING HARNESS (ZPFW2) FILE #E86140. CSA LABEL MUST BE ON SHIPPING CARTON.
- PACKAGE COMPLETED ASSY IN AN APPROPRIATELY SIZED ANTI-STATIC BAG.
- INSTALL DUST COVER OVER EACH CONNECTOR PRIOR TO SHIPMENT TO CUSTOMER.
- EPROM CONTENT SHALL BE COMPLIANT WITH SFF-8636 AND SFF-8024 FOR SAS 3.0.
- CAUTION: ANTI-STATIC CONTROL MEASURES MUST BE OBSERVED DURING THE MANUFACTURE OF THIS ASSEMBLY.
- ALL MATERIALS USED IN THE MANUFACTURE OF THIS ASSEMBLY SHALL COMPLY WITH AMPHENOL REGULATED MATERIALS SPECIFICATION ACS-1152.

NOTES: UNLESS OTHERWISE SPECIFIED



TOLERANCES	DWN	CHK	APVD	TITLE
.00 ± 0.010	12/04/2020	R.LI	12/04/2020	<b>Amphenol AHSP</b> A Division of Amphenol Corporation
.000 ± .003		F.HONG		200 Innovative Way, Suite 201, Norwalk, CT 06851-8796-3000
.0000 ± 0.0001		W.ZHANG	12/04/2020	CABLE ASSEMBLY, MINISAS HD TO MINISAS HD 4X, 28AWG, SAS 3.0, 12Gbps
ANGLES ± 1.0°				

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES

PART NO.	SEE TABLE 1	REV	N/A
DRAWING NO.	C-NBCCDB-C199	REV	C
SIZE	D	SCALE	1:1
Sheet	1	OF	1