

ITEM	DRAWING	REV	DESCRIPTION	MATERIAL	QTY.	NOTE
3		A1	Support Panel	SPCC	1	Black
2		A1	Back Panel	SPCC	1	Black
1		A1	Front Panel	Plastic	1	Black

ProLabs

MAT'L		PRODUCT NO.	-PPA-24P180C6A
UNITS	mm	PRODUCT NAME	19-inch Cat6A 24-Port Angled 1U Patch Panel with 180 Degree Keystones
SCALE	1:1	DRAWING NO.	
TYPE OF PROJECTION		SHEET 1 OF 1	REV A1

NOTE:
1. The parts have no obvious indentation, remove burrs, and blunt at acute angles

2. After spraying, the parts are smooth and clean, without appearance defects such as leakage bottom

3. The silk screen must be clear and free of rough edges









ELECTRICAL:

1.VOLTAGE RATING:	125 VAC RMS
2.CURRENT RATING:	1.5AMP
3.CONTACT RESISTANCE:	100 MILLIOHMS MAX @ 500 VDC
4.INSULATION RESISTANCE:	1000 MEGOHMS MIN
5.INSULATION STRENGTH:	750 VAC RMS 60Hz,1MIN

ENVIRONMENTAL:

1.STORAGE:	-40℃ TO +85℃
2.OPERATION:	0℃ TO 70℃

CONFORM TO TIA/EIA 568BC.2.

MECHANICAL:

1.HOUSING MATERIAL:	PC
2.INSERT MATERIAL:	PBT
3.PCB MATERIAL:	FR-4 THICKNESS:1.6mm
4.CONTACT MATERIAL:	PHOSPHOR BRONZE STAMP PIN T=0.35mm
5.IDC CONTACT MATERIAL:	PHOSPHOR BRONZE T=50-80u NICKEL PLATING
6.WIRE:	AWG 22~26

ProLabs

MATERIAL		UNIT	MM	SCALE	1:1
DIMENSIONAL TOLERANCE X.X ±0.3 X.XX ±0.10 X.XXX ±0.050 ANGLE 1°		THIRD ANGLE PROJECTION		DRAWN CHECK APPROVAL	