

RoHS Compliance

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
C	△	12/03'13	Update the drawing	Jacky
D	△	11/18'14	change the product description ,change the structure	Chenhao
E	△	04/15'15	Add the safety certification icon	Chenhao
F	△	01/12'16	Update drawing	Chenhao
G	△	12/23'21	Add the safety certification icon and update drawing	Johnson
G1	△	06/26'25	Update the drawing	Jesse

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ① Terminal body: PA66 (UL94V-0)
- Item ② Terminal : PhBz,Tin plated.
- Item ③ Terminal cover : PA66 (UL94V-0)

Electrical	cULus	TUV(EN/IEC60998-2-2)
● Voltage rating:	150V	130V
● Current rating:	7A	9A
● Wire range:		
Solid wire(AWG):	18-22	0.34-0.75mm ²
● Wire strip length:	5-6mm	
● Withstanding Voltage:	1.3KV	1.25KV
● Operating temperature:	-40°C to +115°C	
△ Safety approval : 		
● Staying power between the under body and the above body:8kgf.cm		
● Staying power between the body and the cover:2.5kgf.cm		
● Critical dimension: ▲		

PART No.:

△ 2 △ 6 NS XX 00X 0 XXXX G

No. of poles
01...1 pole
02...2poles
upto 4poles

- 0: Black
- 2: Red
- 3: Orange
- 4: Yellow
- 5: Green(RAL6018/T)
- 6: Blue (RAL5015/A)
- 8: Grey(RAL7004/P)
- 9: White






△ 6 C:Multiple colors

G:RoHS compliant

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
with hole

Section B-B

Section A-A



N=Number of poles

DIM	TOL			
	1P	2P	3P	4P
Dim P N×5.75	±0.1	±0.3	±0.4	±0.5
Dim Q N×5.75+1	±0.1	±0.3	±0.4	±0.5

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD.

TITLE	NS5.75 series (solid block with hole) △			
PART NO.	NSXX00X0XXXXG △		DWG NO.	8NS0004
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.
		Jesse 2025.06.26	Johnson 2021.12.23	
SHEET: 01/01				REV.: G1
				Tolerance
				X. ±0.50
				X.X ±0.30
				X.XX ±0.10
				X° ±1°