

Technical data sheet

Flexible Single Conductor Hook Up Wire · Multi-Norm

LUTZE Single Conductor Hook Up Wire With UL/CE/MTW and HAR Approvals



Identification

Type	EA HAR-UL 1×0,75 GE
Part No.	A61910

Product version

Datasheet version	00
-------------------	----

Use/Application/Properties

Application	• Multi-rated single-conductor cable for wiring cabinets and use in electrical and electronic equipment • Specially suited for machines exported to Europe (HAR) and North America (UL MTW) • MTW Machine Tool Wire
Properties	• Fine stranding class 5, per VDE 0295 • Very flexible for easy installation • Free from silicone paint wetting impairment substances (LABS-free) • Conditionally resistant to oils, solvents, acids and bases • MTW rated • RoHS compliant

Construction

Description	SINGLE CONDUCTOR HOOK UP WIRE MULTI-NORM
Number of conductors/cross-section	1×0.75
Number of conductors	1
Cross-section, metric	0.75 mm ²
Cross-section AWG	AWG 19
Outer Ø	2.7 mm
Outer Ø	0.106 inch

Construction Element 1

Element construction	AWG19/1C
Conductor	CU-wire tin-plated
Conductor category	Finely stranded DIN VDE 0295 IEC 60228, Class 5
Conductor marking	yellow

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA
Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223
www.lutze.com • info@lutze.com

24.01.2023 • Subject to technical modification

Part No. [A61910](#) • Datasheet version: 00

page 1 of 2



SYSTEMATIC TECHNOLOGY

Technical data sheet

Flexible Single Conductor Hook Up Wire · Multi-Norm

Conductor insulation	PVC
Conductor insulation standard	UL 1581 Class 43 heat and humidity resistant

Technical data

Rated voltage U_N	H05V2-K 300/500 V H07V2-K 450/750 V 600 V UL MTW 600 V UL AWM 105 °C
Test voltage type	AC 3000 V
Temperature range moving	-5 °C ... +105 °C
Temperature range fixed	-40 °C ... +105 °C
Minimum bending radius fixed	5×cable OD

Technical Data Element 1

Element construction	AWG19/1C
Insulation resistance at 20 °C	20 MΩ×km

Approvals/Standards

Approvals	HAR: HD 21.3 S3 UL 1063 MTW Listed UL AWM RoHS REACH
UL style	AWM 1015
Conformity	CE RoHS REACH
Burning behavior according to	UL VW-1 IEC 60332-1

General

Note	CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU
------	--