




ELECTRICAL:
1.CURRENT RATING: 1.5AMP
2.CONTACT RESISTANCE: 100 MILLIOHMS MAX @ 500 VDC
3.INSULATION RESISTANCE: 1000 MEGOHMS MIN
4.INSULATION STRENGTH: 750 VAC RMS 60Hz,1MIN

ENVIRONMENTAL:
1.STORAGE: -40°C TO +70°C
2.OPERATION: -20°C TO 60°C
COMPLY WITH TIA/EIA 568C.2 INTERNATIONAL STANDARD

MECHANICAL:
1.IDC HOUSING MATERIAL: PBT
2.PANEL FRAME MATERIAL: SPCC,BLACK OR INDUSTRIAL GREY
ELECTROSTATIC POWDER COATING
750 TIMES MIN
3.RJ45 JACK LIFE: 200 TIMES MIN
4.IDC LIFE: 200 TIMES MIN
5.CONTACT MATERIAL: PHOSPHOR BRONZE STAMP PIN T=0.30mm
6.IDC CONTACT MATERIAL: PHOSPHOR BRONZE NICKEL PLATING
7.WIRE: AWG 23~24

3		A1	Support Bar	SPCC	1	Black Powder Coat
2		A1	Keystone Jack	Plastic	24	
1		A1	Front Panel	SPCC	1	Black Powder Coat
ITEM	DRAWING	REV	DESCRIPTION	MATERIAL	QTY.	NOTE

MAT'L		PRODUCT NO.	C-PPA-24PTKSC6A		
UNITS	mm	PRODUCT NAME	19-inch Cat6A 24-Port Angled 1U Patch Panel with Removable tool-less Keystone Sections		
SCALE	1:1	DRAWING NO.			
TYPE OF PROJECTION			SHEET 1 OF 1	REV	