

Fuseless motor starter Reversing operation 600VAC Size S0 2.2-3.2A
110/120VAC 50/60HZ screw connection For 35 mm rail-mounting Type of
coordination 2 IQ = 150 KA Also full fills type Of coordination 1 1NO+1NC (MSP)
1NO+1NC (per contactor)

product brand name	SIRIUS
product designation	non-fused motor starter 3RA2
design of the product	reversing starter
manufacturer's article number	
• of the supplied contactor • of the supplied circuit-breakers • of the supplied RH assembly kit • of the supplied busbar adapter • of the supplied link module • of the supplied DIN-rail adapter	3RT2023-1AK60 3RV2011-1DA15 3RA2923-1BB1 3RA2922-1AA00 3RA2921-1AA00 3RA2922-1AA00
General technical data	
size of the circuit-breaker	S00
size of load feeder	S0
product extension auxiliary switch	Yes
insulation voltage with degree of pollution 3 at AC rated value	690 V
degree of pollution	3
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	6 g / 11 ms
mechanical service life (operating cycles) of contactor typical	10 000 000
type of coordination	2
Substance Prohibitance (day/month/year)	03/01/2017
Net Weight	1.45 kg
Ambient conditions	
ambient temperature	
• during operation • during storage • during transport	-20 ... +60 °C -50 ... +80 °C -55 ... +80 °C
Main circuit	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	2.2 ... 3.2 A
operating voltage	
• rated value • at AC-3 rated value maximum	690 V 690 V
operating frequency rated value	50 ... 60 Hz
operational current at AC-3 at 400 V rated value	2.7 A
operating power at AC-3	
• at 400 V rated value • at 500 V rated value	1 100 W 1 500 W
Control circuit/ Control	
control supply voltage at AC	
• at 50 Hz rated value • at 50 Hz rated value • at 60 Hz rated value • at 60 Hz rated value	110 V 88 ... 121 V 120 V 96 ... 132 V
apparent holding power of magnet coil at AC	7.2 VA
inductive power factor with the holding power of the coil	0.28

Auxiliary circuit			
number of NC contacts for auxiliary contacts		3	
number of NO contacts for auxiliary contacts		3	
Protective and monitoring functions			
trip class		CLASS 10	
design of the overload release		thermal (bimetallic)	
response value current of instantaneous short-circuit trip unit		41.6 A	
UL/CSA ratings			
full-load current (FLA) for 3-phase AC motor			
• at 480 V rated value		2.8 A	
• at 600 V rated value		3.16 A	
yielded mechanical performance [hp]			
• for single-phase AC motor			
— at 110/120 V rated value		0.1 hp	
— at 230 V rated value		0.25 hp	
• for 3-phase AC motor			
— at 200/208 V rated value		0.5 hp	
— at 220/230 V rated value		0.75 hp	
— at 460/480 V rated value		1.5 hp	
— at 575/600 V rated value		2 hp	
Short-circuit protection			
product function short circuit protection		Yes	
design of the short-circuit trip		magnetic	
conditional short-circuit current (Iq)			
• at 400 V according to IEC 60947-4-1 rated value		153 000 A	
Installation/ mounting/ dimensions			
mounting position		vertical	
fastening method		snap-on fastening on 35 mm DIN rail	
height		265 mm	
width		90 mm	
depth		120 mm	
required spacing			
• for grounded parts			
— forwards		10 mm	
— backwards		0 mm	
— upwards		30 mm	
— at the side		9 mm	
— downwards		10 mm	
• for live parts			
— forwards		10 mm	
— backwards		0 mm	
— upwards		30 mm	
— downwards		10 mm	
— at the side		9 mm	
Connections/ Terminals			
type of electrical connection for main current circuit		screw-type terminals	
type of connectable conductor cross-sections for main contacts stranded		1 ... 10 mm², 2x (2.5 ... 6 mm²)	
connectable conductor cross-section for main contacts finely stranded with core end processing		1 ... 6 mm²	
Safety related data			
proportion of dangerous failures with high demand rate according to SN 31920		73 %	
B10 value with high demand rate according to SN 31920		1 000 000	
Electrical Safety			
protection class IP on the front according to IEC 60529		IP20	
touch protection on the front according to IEC 60529		finger-safe, for vertical contact from the front	
Approvals Certificates			
Environment	General Product Approval	For use in hazard-	other

[Environmental Con-
firmations](#)



[Confirmation](#)

other

[Confirmation](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2225-1DB23-0AK6>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2225-1DB23-0AK6>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2225-1DB23-0AK6&lang=en

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2225-1DB23-0AK6>

Characteristic curves

https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>

last modified:

4/4/2026