





Recommended
Panel Cut-Out



M8-XXPMMP-SF800I

XX: No. Of Pin-



Note:
 * RoHS Compliant
 *  Important dimension
 * Waterproof rate: IP68, unmated 1m/24h
 * Connector
 Housing: Thermoplastic, Black
 Pin: Copper alloy, Gold plated
 * Shell: Metal
 * Nut: Metal
 * O-Ring: Rubber, Green
 * For panel thickness: 2.0~4.0mm
 * For pcb thickness max: 1.6mm
 * Nut is packed separately in pe bag

P / N	L (mm)
M8-06PMMP-SF800 I	7.80
M8-04PMMP-SF800 I	8.90
M8-03PMMP-SF800 I	8.90

UNIT: mm				TITLE N SEN, M8, SCREW RECEPTACLE, M, M, PCB S			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Andy		DATE 2026/03/05				
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±				SCALE 2:1		SIZE A4			SHEET 1 OF 2		DWG NO M8-XXPMMP-SF8001		CHECKED BY Yunchen		DATE 2026/03/05		
				REV. B		WC-REV. A.7			QC: Inspection item		CUSTOMER ALTW		APPROVED BY Aric		DATE 2026/03/05		

W10814-03-西醫01A

	1	2	3	4	5	6	7	8
F								
E								
D								
C	3P 4P 6P							
B	PCB Layout 3P 4P 6P							
A	UNIT:mm TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1° TITLE N SEN, M8, SCREW RECEPTACLE, M, M, PCB S SCALE 1:1 REV. B SIZE A4 WC-REV. A.7 SHEET 2 OF 2 QC: Inspection item Amphenol LTW 安費諾亮泰企業股份有限公司 ITEM NO M8-XXPMMP-SF8001 CUSTOMER ALTW DRAWN BY Andy CHECKED BY Yunchen APPROVED BY Aric DATE 2026/03/05 DATE 2026/03/05 DATE 2026/03/05							
	1	2	3	4	5	6	7	8

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.