


Coach™ WiFi 6E Multiband MIMO Antennas for Permanent Mount Applications

Combination Antennas – Cellular, WiFi 6E

PCTHPMIMO-3-SF, PCTHPMIMO-2-SF



Description

Combination permanent mount antenna provides high data rate connectivity for mobile applications

Technologies

- 4G/5G LTE MIMO Cellular
- WiFi 6E

Features

- No tune, multiband coverage
- Easy installation using metal stud mount
- UV-resistant white or black housing options
- Uses high performance, low loss cable and high quality connectors
- IP67 compliant design provides maximum protection against water or dust ingress



Coach™ WiFi 6E Multiband MIMO Antennas for Permanent Mount Applications

Combination Antennas – Cellular, WiFi 6E

The low-profile, permanent mount Coach™ PCTHPMIMO-SF platform antennas enable high data rate connectivity for fleet, rail, mass transit, public safety, and M2M applications. The platform combines multiple antenna elements to deliver multiband coverage in one IP67-rated housing. A single stud mount cable exit simplifies installation.

Features

- Multiband coverage – 2.3-2.8 GHz and 4.9-5.9 GHz frequencies
- Maximum RF system efficiency – Dual-band integrated elements are terminated with high performance, low loss RG-58/U stranded cable and high quality connectors
- Ease of installation and replacement – Metal stud mount with slotted jam nut provides single cable exit
- Low profile – for maximum installation flexibility
- Withstands severe environmental conditions – IP67 compliant design protects against water or dust ingress
- Selection – UV-resistant white or black housing

Applications

- Fleet
- Rail
- Mass transit
- Public safety
- M2M

Certifications



Coach™ WiFi 6E Multiband MIMO Antennas for Permanent Mount Applications

Combination Antennas – Cellular, WiFi 6E

Standard Configurations

Model	MIMO Elements	Cable	Connector ²	Mount
PCTHPMIMO-3-SF	3	Three (3) 17-foot Pro-Flex™ Plus 195 stranded cable leads	Reverse Polarity SMA Male	1-inch hole (25.4 mm) slotted stud mount with 3/4-16 UNF slotted hex-nut
PCTHPMIMO-2-SF	2	Two (2) 17-foot Pro-Flex™ Plus 195 stranded cable leads	Reverse Polarity SMA Male	1-inch hole (25.4 mm) slotted stud mount with 3/4-16 UNF slotted hex-nut

Electrical Specifications – RF Antennas

Model	Frequency Ranges	Gain ¹	VSWR	In-Band Isolation Between Elements	E-Plane Beamwidth	Polarization	Max. Power
PCTHPMIMO-3-SF	2.3-2.8 GHz 4.9-5.9 GHz	1.5 dBi 0.5 dBi	< 1.8:1	23 dB 26 dB	30° 25°	Vertical, linear	25 watts
PCTHPMIMO-2-SF	2.3-2.8 GHz 4.9-5.9 GHz	1.5 dBi 0.5 dBi	< 1.8:1	23 dB 26 dB	30° 25°		

Mechanical and Environmental Specifications (All Models)

Specification	Measurement
Dimensions	5.4 OD x 2.7 in H (137 x 67 mm)
Housing Material	White UV-Stable Rugged Thermoplastics ³
Temperature Range	-40°C to +80°C
Ingress Protection	IP67 ²

¹Measured at the end of the coax.

²When properly installed on rooftop surface, according to PCTEL installation instructions

³Black radome option available. Add "B" prefix to part number for black radome option.

CONTACT US

**For more information about
this product contact your
sales representative or visit
> pctel.com/antenna-products**

Solving Complex Wireless Challenges

PCTEL, an Amphenol company, is a leading global provider of wireless technology solutions, including purpose-built Industrial IoT devices, antenna systems, and test and measurement products. Trusted by our customers for decades, we solve complex wireless challenges to help organizations stay connected, transform, and grow.



PCTEL, Inc.

T: +1 630 372 6800 | pctel.com

Specifications subject to change without notice. PCTEL® are trademarks or registered trademarks of PCTEL, Inc. 3M® is a registered trademark of 3M. ©2025 PCTEL, Inc. All rights reserved. (August 2025)