



ASIsafe SlimLine Compact module SC17.5F digital safety 2 F-DI, IP20 2 x input for mechanical sensors spring-type terminals Overall width 17.5 mm

product designation	Slimline Compact I/O module for use in the control cabinet
design of the product	AS-i SC17.5F, 2F-DI
product type designation	3RK1
design of the device type	standard slave
AS-Interface device profile	S-0.B.F
ID1 code	F; Factory setting, changeable
operating voltage according to AS-Interface specification	18 ... 31.6 V
product function suitable for AS-i Power24V	Yes
consumed current from profile conductors of the AS-Interface	
• at 30 V maximum	50 mA
• at 24 V with AS-i Power24V maximum	50 mA
type of address setting of the AS-i devices	via front addressing socket
Substance Prohibitance (day/month/year)	05/01/2012
SVHC substance name	Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol CAS-No. 119-47-1
Net Weight	0.137 kg
reference code	
• according to EN 61346-2	K
• according to DIN 40719 extended according to IEC 204-2 according to IEC 750	A
shock resistance	15 g / 11 ms (modules) or 10 g / 11 ms (modules with device connector)
Digital Inputs	
number of digital inputs	0
number of digital inputs safety-related	2
type of input characteristic	mechanical contacts
Digital Outputs	
number of digital outputs	0
Analog inputs	
number of analog inputs	0
Analog outputs	
number of analog outputs	0
IEC 62061	
PFHD with high demand rate according to IEC 62061	4.5E-9 1/h
ISO 13849	
performance level (PL) according to EN ISO 13849-1	e
category according to EN ISO 13849-1	up to Category 4

IEC 61508	
Safety Integrity Level (SIL) according to IEC 61508	3
PFDavg with low demand rate according to IEC 61508	5E-6
Safe failure fraction (SFF)	99 %
T1 value for proof test interval or service life according to IEC 61508	20 a

Device connector

ampacity of the interface to the device connector • for AS-Interface	2 A
--	-----

Installation/ mounting/ dimensions

fastening method	screw and snap-on mounting
height	100 mm
width	17.5 mm
depth	120 mm

Ambient conditions

ambient temperature • during operation • during storage	-25 ... +70 °C -40 ... +85 °C
--	----------------------------------

Connections/ Terminals

type of electrical connection of the inputs and outputs	spring-loaded terminal (push-in)
type of connectable conductor cross-sections • solid • finely stranded with core end processing • finely stranded without core end processing • for AWG cables solid • for AWG cables stranded	1x (0.5 ... 1.5 mm²), 2x (0.5 ... 1.5 mm²) 1x (0,25 ... 1,0 mm²), 2x (0,25 ... 1,0 mm²) 1x (0.5 ... 1.5 mm²), 2x (0.5 ... 1.5 mm²) 1x (20 ... 16), 2x (20 ... 16) 1x (20 ... 16), 2x (20 ... 16)

Approvals Certificates

Environment	General Product Approval
-------------	--------------------------

[Environmental Confirmations](#)



EMV	Test Certificates	Maritime application
-----	-------------------	----------------------



[Type Test Certificates/Test Report](#)



other	Industrial Communication
-------	--------------------------

[Confirmation](#)



Further information

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1205-0BG00-2AA2>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1205-0BG00-2AA2>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK1205-0BG00-2AA2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1205-0BG00-2AA2&lang=en





last modified:

5/8/2026 