



!!! phased-out product !!! The preferred successor is 6ES7141-5BF00-0BL0 IO-Link module K20, digital 8 DI, IP67, 8x 1 input sensor supply max. 400 mA 8x M8 socket standard assignment

General technical data		
product designation		IO-Link module K20
design of the product		8 digital inputs
display version		green LED for each channel green/red dual LED green/red dual LED
- as status display of the inputs/outputs - as status display of the input/output link communication - as status display of the input/output link device		
evaluatable diagnostic message via input/output link		overload/short-circuit sensor supply, internal error
protection class IP		IP67
product function control circuit interface with IO link		Yes
type of voltage supply via input/output link master		Yes
installation altitude at height above sea level maximum	m	4 000
ambient temperature		
- during storage - during operation	°C	-40 ... +85
	°C	-25 ... +70
EMC immunity according to IEC 60947-1		ambience A (industrial sector)
EMC emitted interference according to IEC 60947-1		CISPR11, ambience A (industrial sector)
reference code according to DIN 40719 extended according to IEC 204-2 according to IEC 750		A
reference code according to EN 61346-2		K
Inputs/ Outputs		
number of digital inputs		8
number of digital outputs		0
type of parameterization		adjustable for each module (1 ms, 3 ms, 15 ms, 20 ms) adjustable for each input
- of the input delay time - of the inverting of the input signal		
ampacity of the sensor supply		
- maximum - of socket 1 to 4 maximum - of socket 5 to 8 maximum	mA	400
	mA	200
	mA	200
input current at digital input		
- initial value for signal<1>-recognition - full-scale value for signal<0> recognition	mA	11
	mA	1.5
input voltage at digital input 1 initial value for signal<1>-recognition	V	10
Supply voltage		
type of voltage of the supply voltage		DC
supply voltage		
1 at DC rated value	V	24

- at DC rated value
- minimum permissible
- maximum permissible

V	18
V	30

Installation/ mounting/ dimensions

fastening method		frontal or lateral wall mounting
width	mm	20
height	mm	164
depth	mm	45

Connections/ Terminals

number of input/output sockets		8
design of the pin assignment of the inputs		standard assignment
contact assignment		
• of socket 1 at PIN 1		sensor supply +
• of socket 1 at PIN 3		sensor supply -
• of socket 1 at PIN 4		IN1
• of socket 2 at PIN 1		sensor supply +
• of socket 2 at PIN 3		sensor supply -
• of socket 2 at PIN 4		IN2
• of socket 3 at PIN 1		sensor supply +
• of socket 3 at PIN 3		sensor supply -
• of socket 3 at PIN 4		IN3
• of socket 4 at PIN 1		sensor supply +
• of socket 4 at PIN 3		sensor supply -
• of socket 4 at PIN 4		IN4
• of socket 5 at PIN 1		sensor supply +
• of socket 5 at PIN 3		sensor supply -
• of socket 5 at PIN 4		IN5
• of socket 6 at PIN 1		sensor supply +
• of socket 6 at PIN 3		sensor supply -
• of socket 6 at PIN 4		IN6
• of socket 7 at PIN 1		sensor supply +
• of socket 7 at PIN 3		sensor supply -
• of socket 7 at PIN 4		IN7
• of socket 8 at PIN 1		sensor supply +
• of socket 8 at PIN 3		sensor supply -
• of socket 8 at PIN 4		IN8

Certificates/ approvals

certificate of suitability		CE		
General Product Approval			EMV	other



[Confirmation](#)

other	Environment
-------	-------------



[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage


<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK5010-0CA00-0AA0>



last modified:

4/2/2025 