

NC4650ZA330D-EV

Ultra-Low Quiescent Current ($I_q = 70\text{nA}$) Boost Switching Regulator with Low Ripple Mode

FEATURES

- Operating Junction Temperature Range:
-40 °C to 125 °C
- Input Voltage Range (Maximum Rating):
0.6 V to 5.5 V (6.5 V)
- Startup Voltage:
Typ. 0.8 V
- Output Voltage Range: 1.8 V to 5.0 V (Int. Fixed)
- Quiescent Current (V_{OUT}):
Normal Mode: Typ. 70 nA
Low Ripple Mode: Typ. 90 μA
- Shutdown Current:
Typ. 50 nA
- Efficiency ($V_{IN}=1.5\text{ V}$, $V_{OUT}=3.3\text{ V}$, $I_{OUT}=10\text{ }\mu\text{A}$):
Typ. 85 %
- Switch Current Limit:
Typ. 1 A ($V_{SET} \geq 2.5\text{ V}$)
Typ. 0.65 A ($V_{SET} < 2.5\text{ V}$)
- Thermal Shutdown Function:
Detection Temperature: Typ. 150 °C
Release Temperature: Typ. 100 °C
- Soft Start Function
- Buck Operation or Pass-Through when
 $V_{IN} > V_{OUT}$
- Manual switching between Normal Mode and Low Ripple Mode via MODE Pin
- Multiple versions for shutdown behavior

APPLICATIONS

- IoT Edge Devices
- Devices Powered by Coin/Button/Dry Batteries
- Alarms, Smartwatches etc.


GENERAL DESCRIPTION

The NC4650 is a synchronous rectification boost switching regulator featuring ultra-low quiescent current of 70nA, utilizing a CMOS process. It is optimal for portable devices powered by coin or button batteries.

With high efficiency under light load conditions, it is ideal for intermittent operation applications, ensuring long battery life.


The MODE pin enables the selection of "Low Ripple Mode" for improved load transient response and reduced ripple. The EN pin allows shutdown operations, with options such as V_{IN} - V_{OUT} Complete Disconnect, V_{OUT} discharge, and Pass-Through. Selecting the optimal version according to system sleep conditions enables system optimization.

Package




WLCSP-6-ZA1
1.3 x 0.92 x 0.4 (mm)

TYPICAL APPLICATION



EFFICIENCY TYPICAL CHARACTERISTICS



NC4650ZA $V_{OUT} = 3.3\text{ V}$ MODE = "Low"

■ PRODUCT NAME INFORMATION

Product Name	Package
NC4650ZA330D	WLCSP-6-ZA1

Description of configuration

	Item	Description
330	Output Voltage	Set Output Voltage (V_{SET}): 3.3 V


Version

	EN Pin Function	Operation when Shutdown
D	EN="High" : Shutdown EN="Low" : Active	V_{IN} - V_{OUT} Pass-Through Seamless Pass-Through Function

- For more details on NC4650 IC, please refer to

<https://www.nisshinbo-microdevices.co.jp/en/products/dc-dc-switching-regulator/spec/?product=nc4650>

■ PIN DESCRIPTION (NC4650ZA)



WLCSP-6-ZA1 Pin Configuration

NC4650ZA (WLCSP-6-ZA1) Pin Descriptions

Pin No.	Pin Name	I/O	Description
A1	VOUT	Power	Output Pin
B1	GND	-	Ground Pin
C1	VIN	Power	Power Supply Pin
A2	SW	-	Switching Output Pin Connect to Internal MOSFET Drain
B2	MODE	I	Mode Control Pin Low: Normal Mode, High: Low Ripple Mode
C2	EN	I	Enable Pin NC4650ZAxxxD: Can set the active state with the "Low" input and the shutdown state with the "High" input.

■ ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol	Ratings	Unit
VIN pin Voltage	V _{IN}	-0.3 to 6.5	V
VOU _T pin Voltage	V _{OUT}	-0.3 to 6.5	V
SW pin Voltage	V _{SW}	-0.3 to 6.5	V
EN pin Voltage	V _{EN}	-0.3 to 6.5	V
MODE pin Voltage	V _{MODE}	-0.3 to 6.5	V
Storage Temperature Range	T _{stg}	-55 to 150	°C
Junction Temperature *1	T _J	-40 to 150	°C

ABSOLUTE MAXIMUM RATINGS

Electronic and mechanical stress momentarily exceeded absolute maximum ratings may cause permanent damage and may degrade the lifetime and safety for both device and system using the device in the field. The functional operation at or over these absolute maximum ratings is not assured.

*1 Calculate the power consumption of the IC from the operating conditions, and calculate the junction temperature with the thermal resistance.

Please refer to "THERMAL CHARACTERISTICS" for the thermal resistance under our measurement board conditions

■ RECOMMENDED OPERATING CONDITIONS

	Symbol	Ratings	unit
VIN pin Voltage	V _{IN}	0.6 to 5.5	V
Operating Temperature Range	T _a	-40 to 85	°C
Junction Temperature Range	T _J	-40 to 125	°C

RECOMMENDED OPERATING CONDITIONS

All of electronic equipment should be designed that the mounted semiconductor devices operate within the recommended operating conditions. The semiconductor devices cannot operate normally over the recommended operating conditions, even if when they are used over such conditions by momentary electronic noise or surge. And the semiconductor devices may receive serious damage when they continue to operate over the recommended operating conditions.

■ ELECTRICAL CHARACTERISTICS

For parameter that do not describe the temperature condition, the MIN / MAX value under the condition of $-40^{\circ}\text{C} \leq T_j \leq 125^{\circ}\text{C}$ is described.

Parameter	Symbol	Conditions	MIN	TYP	MAX	Unit
Output Voltage	V _{OUTCM}	PWM, V _{SET} ≥ 2.5V, T _j = 25 °C	x 0.985		x 1.015	V
		PWM, V _{SET} < 2.5V, T _j = 25 °C,	x 0.98		x 1.02	V
		PWM, V _{SET} ≥ 2.5V, -40°C ≤ T _j ≤ 85°C	x 0.975		x 1.025	V
		PWM, V _{SET} < 2.5V, -40°C ≤ T _j ≤ 85°C	x 0.97		x 1.03	V
	V _{OUTDCM}	PFM, V _{IN} = 1.5V		V _{OUTCM} x 1.02		V
Startup Voltage	V _{START}	-40°C ≤ T _j ≤ 85°C		0.8	0.9	V
VIN UVLO	V _{VINUULO}	V _{IN} = falling, V _{OUT} = V _{SET}		0.4	0.6	V
VIN pin Quiescent Current	I _{QVIN}	V _{OUT} = V _{SET} , V _{IN} = 1.5V, V _{MODE} = 0 V, no switching,		0		nA
VOUT pin Quiescent Current	I _{QVOUT}	V _{OUT} = V _{SET} , V _{IN} = 1.5V, V _{MODE} = 0 V, no switching, -40°C ≤ T _j ≤ 85°C		70	300	nA
		V _{OUT} = V _{SET} , V _{IN} = 1.5V, V _{MODE} = V _{IN} , no switching, -40°C ≤ T _j ≤ 85°C		90	180	μA
VIN pin Shutdown Current*1	I _{SDVIN}	V _{IN} = 5.5V V _{EN} = 0V (A, B Version) V _{EN} = 5.5V (C, D Version) -40°C ≤ T _j ≤ 85°C		50	200	nA
VOUT pin Shutdown Current*1	I _{SDVOUT}	V _{IN} = 0V, V _{OUT} = V _{SET} V _{EN} = 0V (A Version) V _{EN} = V _{SET} (C, D Version) -40°C ≤ T _j ≤ 85°C		40	250	nA
EN pin "H" Input Current	I _{ENH}	V _{IN} = V _{EN} = 5.5V -40°C ≤ T _j ≤ 85°C	-40	0	40	nA
EN pin "L" Input Current	I _{ENL}	V _{IN} = 5.5V, V _{EN} = 0V -40°C ≤ T _j ≤ 85°C	-40	0	40	nA
MODE pin "H" Input Current	I _{MODEH}	V _{IN} = V _{MODE} = 5.5V -40°C ≤ T _j ≤ 85°C	-40	0	40	nA
MODE pin "L" Input Current	I _{MODEL}	V _{IN} = 5.5V, V _{MODE} = 0V -40°C ≤ T _j ≤ 85°C	-40	0	40	nA
EN pin "H" Input Voltage *2	V _{ENH}		0.9		5.5	V
EN pin "L" Input Voltage *2	V _{ENL}		0		0.3	V
MODE pin "H" Input Voltage *2	V _{MODEH}		1.0		5.5	V
MODE pin "L" Input Voltage *2	V _{MODEL}		0		0.3	V
SW pin "H" Input Current	I _{SWH}	V _{IN} =V _{SW} =5V, V _{OUT} =0V -40°C ≤ T _j ≤ 85°C		1	350	nA
SW pin "L" Input Current	I _{SWL}	V _{IN} =V _{SW} =0V, V _{OUT} =5V -40°C ≤ T _j ≤ 85°C	-200	-1		nA
On-resistance of High Side MOSFET	R _{ONH}	V _{OUT} =3.3V		0.28		Ω
On-resistance of Low Side MOSFET	R _{ONL}	V _{OUT} =3.3V		0.22		Ω
Thermal Shutdown Detection Temperature	T _{SDDET}			150		°C
Thermal Shutdown Release Temperature	T _{SDREL}			100		°C
Inductor Ripple Current	I _{RIP}	V _{IN} = 1.5V, V _{OUT} = V _{SET}		250		mA


Parameter	Symbol	Conditions	MIN	TYP	MAX	Unit
SW Current Limit	ISWLIM	$V_{SET} \geq 2.5V, V_{IN} = 1.5V$	700	1000	1500	mA
		$V_{SET} < 2.5V, V_{IN} = 1.5V$	450	650	950	mA
On-resistance for Discharger	RONDIS	$V_{IN} = 1.5V$, B Version only		55		Ω
Soft-Start Time	tSTART			0.8	1.5	ms
Pass-Through Mode Detection Voltage	VPTHD	$V_{IN} - V_{OUT}$		0.6	0.8	V
Pass-Through Mode Release Voltage	VPTHR	V_{OUT}		$V_{OUTCM} \times 1.02$		V
Pass-Through Mode Quiescent Current	IQPTML	$V_{MODE} = 0V$, $V_{IN} = V_{SET} + 0.4V$		70		nA
	IQPTMH	$V_{MODE} = V_{IN}$, $V_{IN} = V_{SET} + 0.4V$		90		μA
Buck Mode Detection Voltage	VBKDML	$V_{IN} = \text{Rising or } V_{OUT} = \text{Falling}$ $V_{BKDML} = V_{IN} - V_{OUT}$ $V_{MODE} = 0V$		-0.05		V
	VBKDMH	$V_{IN} = \text{Rising or } V_{OUT} = \text{Falling}$ $V_{BKDMH} = V_{IN} - V_{OUT}$ $V_{MODE} = V_{IN}$		-0.1		V
Buck Mode Release Voltage	VBKRL	$V_{IN} = \text{Falling or } V_{OUT} = \text{Rising}$ $V_{BKRL} = V_{IN} - V_{OUT}$ $V_{MODE} = 0V$		-0.1		V
	VBKRMH	$V_{IN} = \text{Falling or } V_{OUT} = \text{Rising}$ $V_{BKRMH} = V_{IN} - V_{OUT}$ $V_{MODE} = V_{IN}$		-0.2		V

All electrical characteristic parameters that specify the minimum and maximum specifications are tested under the condition of $T_j \approx T_a = 25^\circ C$.

*1 On the VIN and VOUT pins, the shutdown current flows only from the pin with the higher voltage. The pin with the lower voltage is Typ. 0 nA.

*2 When the EN and MODE pins are fixed to the VIN pin, the polarity is forced to be "H" as long as VIN pin voltage within the recommended operating condition. (The A and B version)

Typical Application Circuit



※1 Testing with this EV board, an external attachment might be necessary for evaluation of the correct performance of the NC4650 and already has been attached as C_{dum}.

For evaluation, wiring for power supply or GND will be used. Considering the voltage drop or noise by the wiring, C_{dum} has been mounted on the EV board to obtain the right performance of the NC4650 in the actual PCB layout or measurement unit's wire is very short, and C_{dum} will be unnecessary.


Recommended values for components

Symbol	Capacitance
C _{in1}	10 μ F
C _{out1}	22 μ F
L	2.2 μ H
C _{dum} (※1)	10 μ F*3


The bill of materials will be attached on the shipment of each purchased evaluation board.

■ Evaluation Board / PCB Layout Pattern Example

NC4650ZA (WLCSP-6-ZA1)



Top Layer



Bottom Layer

When designing PCB layout patterns, pay close attention to the following items.

- External components should be placed as close as possible to the IC and on the same side, and the wiring from the IC to the components should be short. In particular, the capacitor C_{IN} connected between V_{IN} and GND and the capacitor C_{OUT} connected between V_{OUT} and GND should be placed at the shortest possible distance from the terminals.
- Current due to switching flows through the power supply wiring, ground wiring and SW pins. If the impedance of the power and ground wiring is high, the potential inside the IC may fluctuate due to the switching current, causing the IC to operate unstable. Therefore, the power and ground wiring should be short and thick.
- The wiring from the SW pin to the inductor is a noise source, so ensure that the current capacity is sufficient to prevent the noise from increasing and that the wiring is not thicker and longer than necessary.



1. The products and the product specifications described in this document are subject to change or discontinuation of production without notice for reasons such as improvement. Therefore, before deciding to use the products, please refer to our sales representatives for the latest information thereon.
2. The materials in this document may not be copied or otherwise reproduced in whole or in part without prior written consent of our company.
3. Please be sure to take any necessary formalities under relevant laws or regulations before exporting or otherwise taking out of your country the products or the technical information described herein.
4. The technical information described in this document shows typical characteristics of and example application circuits for the products. The release of such information is not to be construed as a warranty of or a grant of license under our company's or any third party's intellectual property rights or any other rights.
5. The products listed in this document are intended and designed for use as general electronic components in standard applications (office equipment, telecommunication equipment, measuring instruments, consumer electronic products, amusement equipment etc.). Those customers intending to use a product in an application requiring extreme quality and reliability, for example, in a highly specific application where the failure or misoperation of the product could result in human injury or death (aircraft, spacevehicle, nuclear reactor control system, traffic control system, automotive and transportation equipment, combustion equipment, safety devices, life support system etc.) should first contact us.
6. We are making our continuous effort to improve the quality and reliability of our products, but semiconductor products are likely to fail with certain probability. In order to prevent any injury to persons or damages to property resulting from such failure, customers should be careful enough to incorporate safety measures in their design, such as redundancy feature, fire containment feature and fail-safe feature. We do not assume any liability or responsibility for any loss or damage arising from misuse or inappropriate use of the products.
7. Anti-radiation design is not implemented in the products described in this document.
8. The X-ray exposure can influence functions and characteristics of the products. Confirm the product functions and characteristics in the evaluation stage.
9. WLCSP products should be used in light shielded environments. The light exposure can influence functions and characteristics of the products under operation or storage.
10. There can be variation in the marking when different AOI (Automated Optical Inspection) equipment is used. In the case of recognizing the marking characteristic with AOI, please contact our sales or our distributor before attempting to use AOI.
11. Please contact our sales representatives should you have any questions or comments concerning the products or the technical information.



Nisshinbo Micro Devices Inc.

Official website

<https://www.nisshinbo-microdevices.co.jp/en/>

Purchase information

<https://www.nisshinbo-microdevices.co.jp/en/buy/>