



Load feeder fuseless, Direct-on-line starting 400 V AC, Size S00 0.28...0.40 A 230 V AC screw terminal for installation on standard mounting rail (also fulfills type of coordination 1) Type of coordination 2, I<sub>q</sub> = 150 kA 1 NO (contactor)

|                                                                                     |                                |
|-------------------------------------------------------------------------------------|--------------------------------|
| product brand name                                                                  | SIRIUS                         |
| product designation                                                                 | Direct (on-line) starter       |
| design of the product                                                               | for DIN-rail or screw mounting |
| product type designation                                                            | 3RA21                          |
| manufacturer's article number                                                       |                                |
| • of the supplied contactor                                                         | <a href="#">3RT2015-1AP01</a>  |
| • of the supplied circuit-breakers                                                  | <a href="#">3RV2011-0EA10</a>  |
| • of the supplied link module                                                       | <a href="#">3RA1921-1DA00</a>  |
| <b>General technical data</b>                                                       |                                |
| size of the circuit-breaker                                                         | S00                            |
| size of load feeder                                                                 | S00                            |
| power loss [W] for rated value of the current                                       |                                |
| • at AC in hot operating state per pole                                             | 2 W                            |
| • without load current share typical                                                | 4.2 W                          |
| type of calculation of power loss current-dependent                                 | quadratic                      |
| insulation voltage with degree of pollution 3 at AC rated value                     | 690 V                          |
| surge voltage resistance rated value                                                | 6 kV                           |
| degree of protection NEMA rating                                                    | other                          |
| shock resistance according to IEC 60068-2-27                                        | 6 g / 11 ms                    |
| mechanical service life (operating cycles) of contactor typical                     | 30 000 000                     |
| type of coordination                                                                | 2                              |
| reference code according to IEC 81346-2:2019                                        | Q                              |
| Substance Prohibitance (day/month/year)                                             | 10/01/2009                     |
| Net Weight                                                                          | 0.53 kg                        |
| <b>Ambient conditions</b>                                                           |                                |
| ambient temperature                                                                 |                                |
| • during operation                                                                  | -20 ... +60 °C                 |
| • during storage                                                                    | -50 ... +80 °C                 |
| • during transport                                                                  | -50 ... +80 °C                 |
| temperature compensation                                                            | -20 ... +60 °C                 |
| relative humidity during operation                                                  | 10 ... 95 %                    |
| <b>Main circuit</b>                                                                 |                                |
| number of poles for main current circuit                                            | 3                              |
| design of the switching contact                                                     | electromechanical              |
| adjustable current response value current of the current-dependent overload release | 0.28 ... 0.4 A                 |
| operating voltage                                                                   |                                |
| • rated value                                                                       | 690 V                          |
| • at AC-3 rated value maximum                                                       | 690 V                          |

|                                                                                                                                                                                                                                                                                                                                                                                                      |                                                                                          |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>• at AC-3e rated value maximum</li> </ul>                                                                                                                                                                                                                                                                                                                     | 690 V                                                                                    |
| <b>operating frequency rated value</b>                                                                                                                                                                                                                                                                                                                                                               | 50 ... 60 Hz                                                                             |
| <b>operational current</b>                                                                                                                                                                                                                                                                                                                                                                           |                                                                                          |
| <ul style="list-style-type: none"> <li>• at AC-3 at 400 V rated value</li> </ul>                                                                                                                                                                                                                                                                                                                     | 0.4 A                                                                                    |
| <ul style="list-style-type: none"> <li>• at AC-3e at 400 V rated value</li> </ul>                                                                                                                                                                                                                                                                                                                    | 0.4 A                                                                                    |
| <b>operating power</b>                                                                                                                                                                                                                                                                                                                                                                               |                                                                                          |
| <ul style="list-style-type: none"> <li>• at AC-3 <ul style="list-style-type: none"> <li>— at 400 V rated value</li> </ul> </li> </ul>                                                                                                                                                                                                                                                                | 90 W                                                                                     |
| <ul style="list-style-type: none"> <li>• at AC-3e <ul style="list-style-type: none"> <li>— at 400 V rated value</li> </ul> </li> </ul>                                                                                                                                                                                                                                                               | 90 W                                                                                     |
| <b>Control circuit/ Control</b>                                                                                                                                                                                                                                                                                                                                                                      |                                                                                          |
| <b>type of voltage of the control supply voltage</b>                                                                                                                                                                                                                                                                                                                                                 | AC                                                                                       |
| <b>control supply voltage at AC</b>                                                                                                                                                                                                                                                                                                                                                                  |                                                                                          |
| <ul style="list-style-type: none"> <li>• at 50 Hz rated value</li> </ul>                                                                                                                                                                                                                                                                                                                             | 230 V                                                                                    |
| <ul style="list-style-type: none"> <li>• at 60 Hz rated value</li> </ul>                                                                                                                                                                                                                                                                                                                             | 230 V                                                                                    |
| <b>apparent holding power of magnet coil at AC</b>                                                                                                                                                                                                                                                                                                                                                   | 4.2 VA                                                                                   |
| <ul style="list-style-type: none"> <li>• at 50 Hz</li> </ul>                                                                                                                                                                                                                                                                                                                                         | 4.2 VA                                                                                   |
| <ul style="list-style-type: none"> <li>• at 60 Hz</li> </ul>                                                                                                                                                                                                                                                                                                                                         | 3.3 VA                                                                                   |
| <b>inductive power factor with the holding power of the coil</b>                                                                                                                                                                                                                                                                                                                                     | 0.25                                                                                     |
| <ul style="list-style-type: none"> <li>• at 50 Hz</li> </ul>                                                                                                                                                                                                                                                                                                                                         | 0.25                                                                                     |
| <ul style="list-style-type: none"> <li>• at 60 Hz</li> </ul>                                                                                                                                                                                                                                                                                                                                         | 0.25                                                                                     |
| <b>Auxiliary circuit</b>                                                                                                                                                                                                                                                                                                                                                                             |                                                                                          |
| <b>product extension auxiliary switch</b>                                                                                                                                                                                                                                                                                                                                                            | Yes                                                                                      |
| <b>Protective and monitoring functions</b>                                                                                                                                                                                                                                                                                                                                                           |                                                                                          |
| <b>trip class</b>                                                                                                                                                                                                                                                                                                                                                                                    | CLASS 10                                                                                 |
| <b>design of the overload release</b>                                                                                                                                                                                                                                                                                                                                                                | thermal (bimetallic)                                                                     |
| response value current of instantaneous short-circuit trip unit                                                                                                                                                                                                                                                                                                                                      | 5.2 A                                                                                    |
| <b>UL/CSA ratings</b>                                                                                                                                                                                                                                                                                                                                                                                |                                                                                          |
| <b>full-load current (FLA) for 3-phase AC motor</b>                                                                                                                                                                                                                                                                                                                                                  |                                                                                          |
| <ul style="list-style-type: none"> <li>• at 480 V rated value</li> </ul>                                                                                                                                                                                                                                                                                                                             | 0.4 A                                                                                    |
| <ul style="list-style-type: none"> <li>• at 600 V rated value</li> </ul>                                                                                                                                                                                                                                                                                                                             | 0.4 A                                                                                    |
| <b>Short-circuit protection</b>                                                                                                                                                                                                                                                                                                                                                                      |                                                                                          |
| <b>product function short circuit protection</b>                                                                                                                                                                                                                                                                                                                                                     | Yes                                                                                      |
| <b>design of the short-circuit trip</b>                                                                                                                                                                                                                                                                                                                                                              | magnetic                                                                                 |
| <b>conditional short-circuit current (I<sub>q</sub>)</b>                                                                                                                                                                                                                                                                                                                                             |                                                                                          |
| <ul style="list-style-type: none"> <li>• at 400 V according to IEC 60947-4-1 rated value</li> </ul>                                                                                                                                                                                                                                                                                                  | 150 000 A                                                                                |
| <b>Installation/ mounting/ dimensions</b>                                                                                                                                                                                                                                                                                                                                                            |                                                                                          |
| <b>mounting position</b>                                                                                                                                                                                                                                                                                                                                                                             | vertical                                                                                 |
| <b>fastening method</b>                                                                                                                                                                                                                                                                                                                                                                              | screw and snap-on mounting onto 35 mm DIN rail                                           |
| <b>height</b>                                                                                                                                                                                                                                                                                                                                                                                        | 167 mm                                                                                   |
| <b>width</b>                                                                                                                                                                                                                                                                                                                                                                                         | 45 mm                                                                                    |
| <b>depth</b>                                                                                                                                                                                                                                                                                                                                                                                         | 97 mm                                                                                    |
| <b>required spacing</b>                                                                                                                                                                                                                                                                                                                                                                              |                                                                                          |
| <ul style="list-style-type: none"> <li>• for grounded parts <ul style="list-style-type: none"> <li>— forwards</li> <li>— backwards</li> <li>— upwards</li> <li>— at the side</li> <li>— downwards</li> </ul> </li> <li>• for live parts <ul style="list-style-type: none"> <li>— forwards</li> <li>— backwards</li> <li>— upwards</li> <li>— downwards</li> <li>— at the side</li> </ul> </li> </ul> | 20 mm<br>0 mm<br>50 mm<br>20 mm<br>10 mm<br><br>20 mm<br>0 mm<br>50 mm<br>10 mm<br>20 mm |
| <b>Connections/ Terminals</b>                                                                                                                                                                                                                                                                                                                                                                        |                                                                                          |
| <b>type of electrical connection</b>                                                                                                                                                                                                                                                                                                                                                                 |                                                                                          |
| <ul style="list-style-type: none"> <li>• for main current circuit</li> </ul>                                                                                                                                                                                                                                                                                                                         | screw-type terminals                                                                     |

- for auxiliary and control circuit

screw-type terminals

#### Safety related data

product function suitable for safety function

Yes

#### Electrical Safety

**touch protection on the front according to IEC 60529**

finger-safe, for vertical contact from the front

#### Communication/ Protocol

protocol is supported

- PROFINET IO protocol
- PROFIsafe protocol

No

No

protocol is supported AS-Interface protocol

No

#### Approvals Certificates

Environment

General Product Approval

For use in hazardous locations

[Environmental Confirmations](#)



#### Test Certificates

#### Maritime application

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



#### Maritime application

#### other



[Confirmation](#)

[Confirmation](#)



#### Railway

[Special Test Certificate](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2110-0EA15-1AP0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-0EA15-1AP0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RA2110-0EA15-1AP0&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2110-0EA15-1AP0&lang=en)

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2110-0EA15-1AP0>

Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp\\_prod\\_noCOMP="HAUPT"></mmp\\_prod\\_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>)





last modified:

4/24/2026 