



phase-out type semiconductor relay, 3-phase 3RF2 55 A / 40 °C 48-600 V / 4-30 V DC 2-phase controlled ring cable terminal blocking voltage 1200 V for mounting on available cooling surfaces

product brand name	SIRIUS
product designation	solid-state relay
design of the product	2-pole controlled
product type designation	3RF22
manufacturer's article number	
• _2 of the accessories that can be ordered	3RF2900-0EA18
product designation	
• _2 of the accessories that can be ordered	converter
General technical data	
product function	zero-point switching
power loss [W] for rated value of the current	
• at AC in hot operating state	151 W
• at AC in hot operating state per pole	151 W
• without load current share typical	0.5 W
insulation voltage rated value	600 V
surge voltage resistance of main circuit rated value	6 kV
protection class IP	IP00
protection class IP on the front according to IEC 60529	IP00
shock resistance according to IEC 60068-2-27	15 g / 11 ms
vibration resistance according to IEC 60068-2-6	2 g
reference code according to IEC 81346-2	Q
Substance Prohibitance (day/month/year)	07/01/2006
SVHC substance name	Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1
Net Weight	0.14 kg
Main circuit	
number of poles for main current circuit	3
number of NO contacts for main contacts	2
number of NC contacts for main contacts	0
type of voltage of the operating voltage	AC
operating voltage	
• at AC	
— at 50 Hz rated value	48 ... 600 V
— at 60 Hz rated value	48 ... 600 V
operating frequency rated value	50 ... 60 Hz
relative symmetrical tolerance of the operating frequency	10 %
operating range relative to the operating voltage at AC	

• at 50 Hz • at 60 Hz	40 ... 660 V
operational current rated value maximum	40 ... 660 V
operational current	55 A
• at AC-1 at 400 V rated value • at AC-51 rated value • according to UL 508 rated value	55 A
ampacity maximum	50 A
operational current minimum	55 A
rate of voltage rise at the thyristor for main contacts maximum permissible	500 mA
blocking voltage at the thyristor for main contacts maximum permissible	100 V/μs
reverse current of the thyristor	1 200 V
derating temperature	10 mA
surge current resistance rated value	40 °C
I²t value maximum	600 A
	1 800 A ² ·s
Control circuit/ Control	
type of voltage of the control supply voltage	DC
control supply voltage 1 at DC	4 ... 30 V
control supply voltage at DC	
• initial value for signal <1> detection • full-scale value for signal<0> recognition	4 V
	1 V
control current at minimum control supply voltage	
• at DC	22 mA
control current at DC rated value	30 mA
ON-delay time	1 ms; additionally max. one half-wave
OFF-delay time	1 ms; additionally max. one half-wave
Installation/ mounting/ dimensions	
fastening method side-by-side mounting	Yes
fastening method	screw fixing
design of the thread of the screw for securing the equipment	M4
tightening torque of fixing screw maximum	1.5 N·m
tightening torque [lbf·in] of fixing screw maximum	13 lbf·in
height	95 mm
width	45 mm
depth	47 mm
Connections/ Terminals	
product component removable terminal for auxiliary and control circuit	Yes
type of electrical connection	
• for main current circuit • for auxiliary and control circuit	Ring cable lug connection
	screw-type terminals
type of connectable conductor cross-sections	
• for auxiliary and control contacts — solid — finely stranded with core end processing — finely stranded without core end processing • for AWG cables for auxiliary and control contacts	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1 mm ²)
	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1 mm ²)
	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1 mm ²)
	1x (20 ... 12)
tightening torque	
• for main contacts with screw-type terminals • for auxiliary and control contacts with screw-type terminals	2 ... 2.5 N·m
	0.5 ... 0.6 N·m
tightening torque [lbf·in]	
• for main contacts with screw-type terminals • for auxiliary and control contacts with screw-type terminals	18 ... 22 lbf·in
	4.5 ... 5.3 lbf·in
design of the thread of the connection screw	
• for main contacts	M4

• of the auxiliary and control contacts	M3		
stripped length of the cable • for main contacts • for auxiliary and control contacts	10 mm 7 mm		
UL/CSA ratings			
operational current according to UL 508 rated value	55 A		
Ambient conditions			
installation altitude at height above sea level maximum	1 000 m		
ambient temperature • during operation • during storage	-25 ... +60 °C -55 ... +80 °C		
Electromagnetic compatibility			
conducted interference • due to burst according to IEC 61000-4-4 • due to conductor-earth surge according to IEC 61000-4-5 • due to conductor-conductor surge according to IEC 61000-4-5 • due to high-frequency radiation according to IEC 61000-4-6	2 kV / 5 kHz, behavior criterion 2 2 kV, behavior criterion 2 1 kV, behavior criterion 2 140 dBuV in the frequency range 0.15 ... 80 MHz, behavior criterion 1		
electrostatic discharge according to IEC 61000-4-2	4 kV contact discharging / 8 kV air discharging, behavior criterion 2		
conducted HF interference emissions according to CISPR11	Class A for industrial environment		
field-bound HF interference emission according to CISPR11	Class A for industrial environment		
Short-circuit protection, design of the fuse link			
manufacturer's article number • of full range R fuse link for semiconductor protection at NH design usable • of back-up R fuse link for semiconductor protection at NH design usable • of back-up R fuse link for semiconductor protection at cylindrical design 14 x 51 mm usable • of back-up R fuse link for semiconductor protection at cylindrical design 22 x 58 mm usable	3NE1803-0: These fuses have a smaller rated current than the semiconductor relays 3NE8018-1 3NC1450: These fuses have a smaller rated current than the semiconductor relays 3NC2250: These fuses have a smaller rated current than the semiconductor relays		
manufacturer's article number of the gG fuse at NH design usable • up to 460 V • up to 600 V	3NA3807-6: These fuses have a smaller rated current than the semiconductor relays 3NA3805-6: These fuses have a smaller rated current than the semiconductor relays		
Approvals Certificates			
Environment	General Product Approval		
Environmental Confirmations	    		
General Product Approval	EMV	Test Certificates	other
 	Type Test Certificates/Test Report	Confirmation	Miscellaneous Confirmation
other			
			

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RF2255-3AB45>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RF2255-3AB45>



Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RF2255-3AB45>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RF2255-3AB45&lang=en





last modified:

4/4/2026