



Coupling relay in industrial enclosure 1 changeover contact Wide voltage range 24 V to 240 V AC/DC Screw terminals

product brand name	SIRIUS
product designation	Coupling relay in industrial enclosure
product type designation	3RQ2
General technical data	
product feature protective coating on printed-circuit board	No
consumed active power	1.5 W
insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value	300 V
degree of pollution	3
surge voltage resistance rated value	4 kV
maximum permissible voltage for protective separation - between auxiliary and auxiliary circuit - between control and auxiliary circuit according to IEC 60947-1	300 V 300 V
shock resistance - according to IEC 60068-2-27 - for railway applications according to EN 61373	11 g / 15 ms Category 1, Class B
vibration resistance - according to IEC 60068-2-6 - for railway applications according to EN 61373	10 ... 55 Hz: 0.35 mm Category 1, Class B
switching behavior	monostable
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles) at AC-15 at 230 V typical	100 000
thermal current of the switching element with contacts maximum	5 A
reference code according to IEC 81346-2	K
Substance Prohibitance (day/month/year)	05/31/2018
SVHC substance name	2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1
Net Weight	0.129 kg
Control circuit/ Control	
control supply voltage at AC - at 50 Hz rated value - at 50 Hz - at 60 Hz rated value - at 60 Hz	24 ... 240 V 24 ... 240 V 24 ... 240 V 24 ... 240 V
control supply voltage at DC rated value	24 ... 240 V
control supply voltage at DC	24 ... 240 V
operating range factor control supply voltage rated value at DC	

initial value	0.7
full-scale value	1.1
operating range factor control supply voltage rated value at AC at 50 Hz	
initial value	0.7
full-scale value	1.1
operating range factor control supply voltage rated value at AC at 60 Hz	
initial value	0.7
full-scale value	1.1
ON-delay time	
at AC maximum	10 ms
at DC maximum	10 ms
OFF-delay time maximum	100 ms
Switching Function	
design of the switching function	CO contact
Mechanical data	
product component plug-in socket	No
design of the relay operating mechanism	poled
Short-circuit protection	
design of the fuse link for short-circuit protection of the auxiliary switch required	fuse gL/gG: 6 A
Auxiliary circuit	
material of switching contacts	AgSnO2
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
number of CO contacts for auxiliary contacts	1
contact reliability of auxiliary contacts	one incorrect switching operation of 100 million switching operations (17 V, 5 mA)
type of voltage	AC/DC
ampacity of the output relay at AC-15	
at 24 V at 50/60 Hz	3 A
at 110 V at 50/60 Hz	3 A
at 250 V at 50/60 Hz	3 A
ampacity of the output relay at DC-13	
at 24 V	1 A
at 125 V	0.2 A
at 250 V	0.1 A
Electromagnetic compatibility	
EMC emitted interference according to IEC 60947-1	ambience A (industrial sector)
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
due to burst according to IEC 61000-4-4	2 kV
due to conductor-earth surge according to IEC 61000-4-5	2 kV (line to ground)
due to conductor-conductor surge according to IEC 61000-4-5	1 kV (line to line)
field-based interference according to IEC 61000-4-3	10 V/m
electrostatic discharge according to IEC 61000-4-2	4 kV contact discharging, 8 kV air discharging
Display	
product component LED	Yes
Connections/ Terminals	
product component removable terminal for auxiliary and control circuit	Yes
type of electrical connection	screw terminal
type of connectable conductor cross-sections	
solid	1x (0.5 ... 4 mm²), 2x (0.5 ... 2.5 mm²)
finely stranded with core end processing	1x (0.5 ... 4 mm²), 2x (0.5 ... 1.5 mm²)
for AWG cables solid	1x (20 ... 12), 2x (20 ... 14)
connectable conductor cross-section	
solid	0.5 ... 4 mm²

finely stranded with core end processing maximum	4 mm ²
finely stranded without core end processing minimum	0.5 mm ²
AWG number as coded connectable conductor cross section	
solid	12 ... 20
stranded	12 ... 20
tightening torque with screw-type terminals	0.6 ... 0.8 N·m
stripped length of the cable for auxiliary and control contacts	10 mm

Installation/ mounting/ dimensions

mounting position	any
fastening method	screw and snap-on mounting onto 35 mm DIN rail
height	100 mm
width	22.5 mm
depth	90 mm

Ambient conditions

installation altitude at height above sea level maximum	2 000 m
ambient temperature	
during operation	-40 ... +60 °C
during storage	-40 ... +80 °C
during transport	-40 ... +80 °C
relative humidity during operation	10 ... 95 %

Approvals Certificates

Environment	General Product Approval
--------------------	---------------------------------

[Environmental Confirmations](#)



EMV	Test Certificates	Maritime application
------------	--------------------------	-----------------------------



[Type Test Certificates/Test Report](#)



Maritime application	other	Railway
-----------------------------	--------------	----------------



[Confirmation](#)



[Confirmation](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RQ2000-1AW00>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RQ2000-1AW00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RQ2000-1AW00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RQ2000-1AW00&lang=en



