

Siemens  
EcoTech



circuit breaker 3VA1 IEC Frame 100 breaking capacity class B  $I_{cu}=16 \text{ kA} @ 415 \text{ V}$   
4-pole, line protection TM210, FTFM,  $I_n=80 \text{ A}$  overload protection  $I_r=80 \text{ A}$   
permanently set short-circuit protection  $I_i=10 \times I_n$  N conductor unprotected terminal connection

| Model                                                                                                 |                             |
|-------------------------------------------------------------------------------------------------------|-----------------------------|
| product brand name                                                                                    | SENTRON                     |
| product designation                                                                                   | Molded case circuit breaker |
| design of the product                                                                                 | Line protection             |
| design of the overcurrent release                                                                     | TM210                       |
| protection function of the overcurrent release                                                        | LI                          |
| number of poles                                                                                       | 4                           |
| General technical data                                                                                |                             |
| insulation voltage / rated value                                                                      | 800 V                       |
| operating voltage / at DC / rated value                                                               | 600 V                       |
| operating voltage / at AC / rated value                                                               | 690 V                       |
| power loss [W] / maximum                                                                              | 19.2 W                      |
| mechanical service life (operating cycles) / typical                                                  | 20 000                      |
| electrical endurance (operating cycles) / at AC-1 / at 380/415 V                                      | 9 000                       |
| electrical endurance (operating cycles) / at AC-1 / at 690 V                                          | 6 300                       |
| product feature / for neutral conductors / upgradable/retrofitable / short-circuit and overload proof | No                          |
| ground-fault monitoring version                                                                       | Without                     |
| product function                                                                                      |                             |
| • communication function                                                                              | No                          |
| • other measurement function                                                                          | No                          |
| Net Weight                                                                                            | 1.285 kg                    |
| Current                                                                                               |                             |
| operational current                                                                                   |                             |
| • at 40 °C                                                                                            | 80 A                        |
| • at 45 °C                                                                                            | 80 A                        |
| • at 50 °C                                                                                            | 80 A                        |
| • at 55 °C                                                                                            | 78 A                        |
| • at 60 °C                                                                                            | 77 A                        |
| • at 65 °C                                                                                            | 75 A                        |
| • at 70 °C                                                                                            | 74 A                        |
| Switching capacity according to IEC 60947                                                             |                             |
| switching capacity class of the circuit breaker                                                       | B                           |
| maximum short-circuit current breaking capacity ( $I_{cu}$ )                                          |                             |
| • at 240 V                                                                                            | 25 kA                       |
| • at 415 V                                                                                            | 16 kA                       |

|                                                                                                                                                                                                      |                                                                                                                                                                |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>• at 440 V</li> <li>• at 500 V</li> <li>• at 690 V</li> </ul>                                                                                                 | 8 kA<br>5 kA<br>5 kA                                                                                                                                           |
| operating short-circuit current breaking capacity (Ics) <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> <li>• at 440 V</li> <li>• at 500 V</li> <li>• at 690 V</li> </ul> | 25 kA<br>16 kA<br>8 kA<br>5 kA<br>5 kA                                                                                                                         |
| short-circuit current making capacity (Icm) <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> <li>• at 440 V</li> <li>• at 500 V</li> <li>• at 690 V</li> </ul>             | 52.5 kA<br>32 kA<br>13.6 kA<br>7.5 kA<br>7.5 kA                                                                                                                |
| design of short-circuit protection                                                                                                                                                                   | For switching power values in DC networks, see the 3VA molded case circuit breaker device manual; link to be found under Service & Support in the last chapter |

#### Adjustable parameters

|                                                                                                                                                                         |                |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|
| product feature / for L-tripping / can be switched on/off                                                                                                               | No             |
| adjustable response value setting current (Ir) / of the L-trip / with I2t characteristic <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul> | 80 A<br>80 A   |
| adjustable response value delay time (tr) / for L-tripping / with I2t characteristic <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>     | 1 s<br>1 s     |
| adjustable response value setting current (Ii) / for I-tripping <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                          | 800 A<br>800 A |
| adjustable setting current (InN) / for N-tripping <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                        | 0 A<br>0 A     |
| design of the N-conductor protection                                                                                                                                    | without        |
| product function / grounding protection                                                                                                                                 | No             |

#### Mechanical Design

|                                                                                                                                                 |                    |
|-------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| product component <ul style="list-style-type: none"> <li>• undervoltage release</li> <li>• voltage trigger</li> <li>• trip indicator</li> </ul> | No<br>No<br>No     |
| height [in]                                                                                                                                     | 5.12 in            |
| height                                                                                                                                          | 130 mm             |
| width [in]                                                                                                                                      | 4 in               |
| type of connectable conductor cross-sections / of the round conductor terminal / stranded                                                       | 1 x (1,5 - 70 mm²) |
| width                                                                                                                                           | 101.5 mm           |
| depth [in]                                                                                                                                      | 2.76 in            |
| depth                                                                                                                                           | 70 mm              |

#### Connections

|                                                                                       |                            |
|---------------------------------------------------------------------------------------|----------------------------|
| arrangement of electrical connectors / for main current circuit                       | Front terminal             |
| type of electrical connection / for main current circuit                              | box terminal on both sides |
| design of the surface / of the connections / on the top of the switch (N, 1, 3, 5)    | Silver                     |
| design of the surface / of the connections / on the bottom of the switch (N, 2, 4, 6) | Tin                        |

#### Auxiliary circuit

|                                                |   |
|------------------------------------------------|---|
| number of CO contacts / for auxiliary contacts | 0 |
|------------------------------------------------|---|

#### Accessories

|                                            |    |
|--------------------------------------------|----|
| product extension / optional / motor drive | No |
|--------------------------------------------|----|

#### Environmental conditions

|                                    |        |
|------------------------------------|--------|
| protection class IP / on the front | IP40   |
| ambient temperature                |        |
| • during operation / minimum       | -25 °C |
| • during operation / maximum       | 70 °C  |
| • during storage / minimum         | -40 °C |
| • during storage / maximum         | 80 °C  |

#### Environmental footprint

|                                                          |           |
|----------------------------------------------------------|-----------|
| Environmental Product Declaration(EPD)                   | Yes       |
| global warming potential [CO2 eq] / total                | 190 kg    |
| global warming potential [CO2 eq] / during manufacturing | 4.67 kg   |
| global warming potential [CO2 eq] / during operation     | 186 kg    |
| global warming potential [CO2 eq] / after end of life    | -0.826 kg |
| reference code / according to IEC 81346-2                | Q         |

#### Approvals / Certificates

##### General Product Approval



[Miscellaneous](#)



[Confirmation](#)

##### General Product Approval

##### EMV

##### Test Certificates



EG-Konf.



RCM

[Miscellaneous](#)

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

#### Maritime application



ABS



BUREAU  
VERITAS



DNV



LRS



RMRS

[CCS \(China Classification Society\)](#)

##### other

##### Environment

[Miscellaneous](#)

[Confirmation](#)



[Environmental Confirmations](#)

[Environmental Confirmations](#)



#### Environment



Siemens  
EcoTech



#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)


<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA1080-2ED46-0AA0>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA1080-2ED46-0AA0>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[https://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA1080-2ED46-0AA0](https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA1080-2ED46-0AA0)





4/18/2026 

