



switch disconnecter 3VA1 IEC frame 160 4-pole SD100, In=100A without overload protection w/o short-circuit protection nut keeper kit

Model	
product brand name	SETRON
product designation	Molded case circuit breaker
product version	General applications
design of the product	in MCCB design
number of poles	4
design of the auxiliary release	without
design of the auxiliary switch	Without
General technical data	
insulation voltage / rated value	800 V
operating voltage / at DC / rated value	600 V
operating voltage / at AC / rated value	690 V
surge voltage resistance / rated value	8 kV
power loss [W] / maximum	38 W
mechanical service life (operating cycles) / typical	20 000
type of device	fixed mounting
suitability for use / switch disconnecter	Yes
suitability for use / main switch	Yes
suitability for use / EMERGENCY OFF switch	Yes
suitability for use / maintenance/repair switch	Yes
product function / communication function	No
Net Weight	1.154 kg
Current	
short-time withstand current (Icw) / at AC / limited to 0.5 s / rated value	2 kA
operational current / rated value	100 A
operational current • at 40 °C • at 45 °C • at 50 °C • at 55 °C • at 60 °C • at 65 °C • at 70 °C	100 A 100 A 100 A 100 A 100 A 100 A 100 A
let-through I2t value / at AC-23 B • at 400 V / maximum permissible	475 000 A²·s

• at 500 V / maximum permissible	475 000 A²·s
• at 690 V / maximum permissible	475 000 A²·s
let-through current (Ic) / at AC-23 B	
• at 400 V / maximum permissible	20 kA
• at 500 V / maximum permissible	3 kA
• at 690 V / maximum permissible	3 kA

Switching capacity according to IEC 60947

conditional short-circuit current (Iq) / with line-side fuse protection	
• at 415 V / by LV HRC fuse link 3NA, 3ND (sizes 00/000, 1, 2, type gL/gG) / rated value	70 kA

Mechanical Design

overvoltage category	IV
fastening method	screw fixing
fastening method / 4-hole front mounting	Yes
fastening method / front mounting with central attachment	No
fastening method / rail mounting	No
product component	
• undervoltage release	No
• voltage trigger	No
• undervoltage release with leading contact	No
• trip indicator	No
product feature / interlock	No
height	130 mm
width	101.5 mm
depth	70 mm
display version / for switch position indicator	Handle switch position On, Trip, Off
design of the actuating element	toggle handle
type of the driving mechanism / motor drive	No

Connections

arrangement of electrical connectors / for main current circuit	Front terminal
type of electrical connection / for main current circuit	busbar connection
design of the surface / of the connections / on the top of the switch (N, 1, 3, 5)	silver
design of the surface / of the connections / on the bottom of the switch (N, 2, 4, 6)	Silver

Auxiliary circuit

number of CO contacts / for auxiliary contacts	0
number of NC contacts / for auxiliary contacts	0
number of NO contacts / for auxiliary contacts	0

Accessories

product extension / auxiliary switch	No
product extension / optional / motor drive	Yes

Environmental conditions

protection class IP / on the front	IP40
ambient temperature	
• during operation / minimum	-25 °C
• during operation / maximum	70 °C
• during storage / minimum	-40 °C
• during storage / maximum	80 °C
reference code / according to IEC 81346-2	Q

Approvals / Certificates

General Product Approval



[Miscellaneous](#)



[Confirmation](#)



General Product Ap-

EMV

Test Certificates

Maritime application

proval			
--------	--	--	--



[Miscellaneous](#)

[Special Test Certificate](#)



Maritime application	other
----------------------	-------



[CCS \(China Classification Society\)](#)

[Miscellaneous](#)

[Confirmation](#)

other	Environment
-------	-------------



[Environmental Confirmations](#)

[Environmental Confirmations](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA1110-1AA42-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA1110-1AA42-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA1110-1AA42-0AA0

CAX-Online-Generator

<https://www.siemens.com/cax>

Tender specifications

<https://www.siemens.com/specifications>

Characteristic curves

https://curves.simar.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>



