




Figure similar

transformer SITAS; phases: 1; Pn/Pn(S6)(kVA): 0.063 /0.19;
Upri(V): 550-525-500-480-460- 440-415-400-380-230-208;
Usec(V): 24; Isec(A): 2.63; F(Hz): 50...60; vector group/shielding
winding: II0 /0; temperature rise/insulation class: 40 /B; IP00;
connection: screw/flat-type connection; mounting: screws / DIN rail;
EN 61558-2-2, -2-6 >UL/CSA-recognized< >control transformer<
>safety transformer<

General technical data		
product designation		transformer SITAS
product brand name		SIDAC
operating apparent power rated value	VA	63
efficiency		0.85
connection method for transformers		II0
certificate of suitability		CE / cRUus
product function		
• temperature monitoring		No
• insulation monitoring		No
• short-circuit and overload proof		No
number of shielding windings		0
short-term vector power	VA	190
relative short-circuit voltage	%	8.4
Inputs		
phase number of the inputs		1
input voltage		
• _1 rated value	V	550
• _2 rated value	V	525
• _3 rated value	V	500
• _4 rated value	V	480
• _5 rated value	V	460
• _6 rated value	V	440
• _7 rated value	V	415
• _8 rated value	V	400
• _9 rated value	V	380
• _10 rated value	V	230
• _11 rated value	V	208
electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60
Outputs		
phase number of the outputs		1
output voltage		
• _1 rated value	V	24
electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50

Ambient conditions		
thermal class according to IEC 60085		B
ambient temperature rated value	°C	40
protection class IP		IP00
Mechanical data		
type of electrical connection		
• at output for main current circuit		screw-type terminals / tab terminals
• at input for main current circuit		screw-type terminals / tab terminals
fastening method		screws / DIN rail
construction form of the iron core		EI 84/28
width	m	0.086
height	m	0.098
depth	m	0.09
Certificates/ approvals		
General Product Approval	other	Environment



[Confirmation](#)



[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AM3242-8DN00-0EA0>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM3242-8DN00-0EA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AM3242-8DN00-0EA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM3242-8DN00-0EA0&lang=en



Typ	Bemes- sungs- leistung kVA ¹⁾	Bezeichnung nach DIN 41 302	b ₁	b ₂	b ₃	b ₄	d ₁	d ₂	h ₁	l ₁	n ₁	n ₂
4AM32	0,063	EI 84/28	86	45	2	34	4,8 x 8,4	M 4	97	86	65	64
4AM34	0,1	EI 84/42	86	51	2	34	4,8 x 8,4	M 4	97	86	65	64
4AM38	0,16	EI 96/44	102	52	5	44	5,8 x 9	M 5	106	98	86	84
4AM40	0,25	EI 96/58	102	59	5	44	5,8 x 9	M 5	106	98	87	84

1) Die Bemessungsleistung gilt nur für Transformatoren mit getrennten Wicklungen (nicht bei Spartransformatoren).

