




Figure similar

transformer SITAS; phases: 1; Pn/Pn(S6)(kVA): 0.315 /1.12;
Upri(V): 230+/-5%; Usec(V): 24; Isec(A): 13.1; F(Hz): 50...60; vector
group/shielding winding: II0 /0; temperature rise/insulation class: 40
/B; IP00; connection: screw/flat-type connection; mounting: DIN rail;
EN 61558-2-2, -2-6 >UL/CSA-recognized< >control transformer<
>safety transformer<

General technical data		
product designation		transformer SITAS
product brand name		SIDAC
operating apparent power rated value	VA	315
efficiency		0.9
connection method for transformers		II0
certificate of suitability		CE / cRUus
product function		
• temperature monitoring		No
• insulation monitoring		No
• short-circuit and overload proof		No
number of shielding windings		0
short-term vector power	VA	1 120
relative short-circuit voltage	%	6.08
Inputs		
phase number of the inputs		1
input voltage		
• _1 rated value	V	242
• _2 rated value	V	230
• _3 rated value	V	218
electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60
Outputs		
phase number of the outputs		1
output voltage		
• _1 rated value	V	24
electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50
Ambient conditions		
thermal class according to IEC 60085		B
ambient temperature rated value	°C	40
protection class IP		IP00
Mechanical data		
type of electrical connection		
• at output for main current circuit		screw-type terminals / tab terminals
• at input for main current circuit		screw-type terminals / tab terminals

fastening method		DIN rail
construction form of the iron core		EI 105/60
width	m	0.107
height	m	0.111
depth	m	0.12

Certificates/ approvals

General Product Approval	other	Environment
--------------------------	-------	-------------



[Confirmation](#)



[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AM4342-4TN00-0EB0>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM4342-4TN00-0EB0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/4AM4342-4TN00-0EB0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM4342-4TN00-0EB0&lang=en



Montagebohrung



① Cage-Clamp-Anschluss

24 A: eindrätig 0,08 bis 4 mm²
feindrätig 0,08 bis 4 mm²

Typ	Bemes- sungs- leistung kVA ¹⁾	Bezeichnung nach DIN 41 302	b ₁	b ₂	d ₁	d ₂	h ₁	l ₁	n ₁	n ₂
4AM23	0,025	EI 60/20	50	39	3,6 x 6	M 3	75	62	39	44
4AM26	0,04	EI 66/22	56	40	4,8 x 8	M 4	79	68	45	50
4AM32	0,063	EI 84/28	86	45	4,8 x 8,4	M 4	97	86	65	64
4AM34	0,1	EI 84/42	86	51	4,8 x 8,4	M 4	97	86	65	64
4AM38	0,16	EI 96/44	102	52	5,8 x 9	M 5	106	98	86	84
4AM40	0,25	EI 96/58	102	59	5,8 x 9	M 5	106	98	87	84
4AM43	0,315	EI 105/60	103	60	5,8 x 9	M 5	111	107	84	81
4AM46	0,4	EI 120/52	102	57	5,8 x 9	M 5	121	122	85	90
4AM48	0,5	EI 120/72	123	67	5,8 x 9	M 5	121	122	104	90
4AM52	0,63	EI 150N/48	111	55	7 x 13	M 6	144	152	90	122
4AM55	0,8	EI 150N/65	128	63	7 x 13	M 6	144	152	106	122
4AM57	1	EI 150N/90	154	66	7 x 13	M 6	144	152	130	122
4AM61	1,6	EI 174/82	155	69	7 x 15	M 6	164	176	112	145
4AM64	2	EI 174/102	177	79	7 x 15	M 6	164	176	149	145
4AM65	2,5	EI 192/110	188	88	9 x 16	M 8	180	194	156	160

1) Die Bemessungsleistung gilt nur für Transformatoren mit getrennten Wicklungen
(nicht bei Spartransformatoren).

last modified:

4/2/2025