



SIMATIC ET 200SP, Signal relay module, RQ CO 4x 24V DC/2A ST, 4 changeover contacts, isolated contacts, packing unit: 1 piece, fits to BU-type A0, Colour Code CC00, substitute value output, module diagnostics for: supply voltage

General information	
Product type designation	RQ CO 4x24VDC/2A ST
HW functional status	From FS02
Firmware version	V0.0
• FW update possible	No
usable BaseUnits	BU type A0
Color code for module-specific color-coded label	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V14
• STEP 7 configurable/integrated from version	V5.5 SP3
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSO	No
Redundancy	
• Redundancy capability	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	50 mA
Power loss	
Power loss, typ.	1.2 W
Address area	
Address space per module	
• Inputs	+ 1 byte for QI information
• Outputs	1 byte

Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	type C
Digital outputs	
Type of digital output	Relays
Number of digital outputs	4
Current-sinking	Yes
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
Short-circuit protection	No
Parallel switching of two outputs	
• for logic links	Yes
• for uprating	No
• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	2 Hz
Total current of the outputs	
• Current per channel, max.	2 A
• Current per module, max.	8 A
Total current of the outputs (per module)	
horizontal installation	
— up to 40 °C, max.	8 A
— up to 50 °C, max.	6 A
— up to 60 °C, max.	4 A
vertical installation	
— up to 30 °C, max.	8 A
— up to 40 °C, max.	6 A
— up to 50 °C, max.	4 A
Relay outputs	
• Number of relay outputs	4
• Rated supply voltage of relay coil L+ (DC)	24 V
• Current consumption of relays (coil current of all relays), max.	40 mA
• Number of operating cycles, max.	500 000
Switching capacity of contacts	
— with resistive load, max.	2 A
— Thermal continuous current, max.	2 A
— Switching current, min.	1 mA; 5 V DC
— Rated switching voltage (DC)	24 V
— Rated switching voltage (AC)	24 V
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	200 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire break	No
• Short-circuit	No
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	No
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	

Potential separation channels			
• between the channels		Yes	
• between the channels and backplane bus		Yes	
• between the channels and the power supply of the electronics		Yes	
Isolation			
Isolation tested with		707 V DC (type test)	
Standards, approvals, certificates			
Suitable for safety functions		No	
Ecological footprint			
• environmental product declaration		Yes	
Global warming potential			
— global warming potential, (total) [CO2 eq]		25.5 kg	
— global warming potential, (during production) [CO2 eq]		3.54 kg	
— global warming potential, (during operation) [CO2 eq]		22.1 kg	
— global warming potential, (after end of life cycle) [CO2 eq]		-0.137 kg	
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.		-30 °C	
• horizontal installation, max.		60 °C	
• vertical installation, min.		-30 °C	
• vertical installation, max.		50 °C	
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.		2 000 m; On request: Installation altitudes greater than 2 000 m	
Absolute humidity			
• dew point, min.		-60 °C; suitable for dry room applications	
Dimensions			
Width		15 mm	
Height		73 mm	
Depth		58 mm	
Weights			
Weight, approx.		30 g	
Classifications			
		Version	Classification
	eClass	16	27-24-26-04
	eClass	14	27-24-26-04
	eClass	12	27-24-26-04
	eClass	9.1	27-24-26-04
	eClass	9	27-24-26-04
	eClass	8	27-24-26-04
	eClass	7.1	27-24-26-04
	eClass	6	27-24-26-04
	ETIM	10	EC001599
	ETIM	9	EC001599
	ETIM	8	EC001599
	ETIM	7	EC001599
	IDEA	4	3566
	UNSPSC	15	32-15-17-05
Approvals / Certificates			
General Product Approval			



[Manufacturer Declaration](#)

[Miscellaneous](#)



General Product Approval

For use in hazardous locations



[China RoHS](#)



For use in hazardous locations

Maritime application

[FM](#)



[NK / Nippon Kaiji Kyokai](#)

Maritime application

Environment



[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)



Environment

[China RoHS](#)

last modified:

2/1/2026