



Figure similar

SIMATIC ET 200SP, CM PTP communication module for serial connection RS-422, RS-485 and RS-232, freeport, 3964 (R), USS, MODBUS RTU master, slave, max. 250 Kbit/s, suitable for BU type A0, pack quantity: 10 units

General information	
Product type designation	CM PtP
Firmware version	
• FW update possible	Yes
usable BaseUnits	BU type A0
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	STEP 7 V17 or higher
• STEP 7 configurable/integrated from version	via GSD as of V5.6 HF4
• PROFIBUS from GSD version/GSD revision	GSD as of Revision 5
• PROFINET from GSD version/GSD revision	GSDML V2.34
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	31 mA
Current consumption, max.	35 mA
Power loss	
Power loss, typ.	0.7 W
Address area	
Address space per module	
• Address space per module, max.	8 byte; performance mode: 32 byte
• Inputs	8 byte; performance mode: 32 byte
• Outputs	0 byte; performance mode: 32 byte
1. Interface	
Interface types	
• RS 485	Yes
• RS 422	Yes
• RS 232	Yes
• Design of the connection	Push-in terminal
Interface types	
RS 232	
• Transmission rate, max.	115.2 kbit/s
• Cable length, max.	15 m

• RS 232 auxiliary signals	RTS, CTS, DTR, DSR, RI, DCD
RS 485	
• Transmission rate, max.	250 kbit/s
• Cable length, max.	1 200 m; 200 m to 1200 m, depending on transmission speed
RS 422	
• Transmission rate, max.	115.2 kbit/s
• Cable length, max.	1 200 m; 200 m to 1200 m, depending on transmission speed
• 4-wire full duplex connection	Yes
• 4-wire multipoint connection	Yes
Protocols	
Integrated protocols	
Freeport	
— Telegram length, max.	2 kbyte; performance mode: receive data max. 24 byte and send data max. 30 byte
— Bits per character	7 or 8
— Number of stop bits	1 or 2 bit
— Parity	None, even, odd, always 1, always 0, any
3964 (R)	
— Telegram length, max.	2 kbyte; performance mode: receive data max. 24 byte and send data max. 30 byte
— Bits per character	7 or 8
— Number of stop bits	1 or 2 bit
— Parity	None, even, odd, always 1, always 0, any
Modbus RTU master	
— Address area	1 to 247, extended 1 to 65535
— max. number of devices	32
Modbus RTU device	
— Address area	1 to 247, extended 1 to 65535
Telegram buffer	
• Buffer memory for telegrams	4 kbyte
• Number of telegrams which can be buffered	255
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
• Diagnostic alarm	Yes
• Hardware interrupt	No
Diagnoses	
• Wire break	Yes
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• for module diagnostics	Yes; green/red DIAG LED
• Receive RxD	Yes; green LED
• Transmit TxD	Yes; green LED
Potential separation	
between backplane bus and interface	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	25.2 kg
— global warming potential, (during production) [CO2 eq]	6.15 kg
— global warming potential, (during operation) [CO2 eq]	19.4 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.289 kg
Ambient conditions	
Ambient temperature during operation	

• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m

Decentralized operation

to SIMATIC S7-300	Yes
to SIMATIC S7-400	Yes
to SIMATIC S7-1200	Yes
to SIMATIC S7-1500	Yes
to standard PROFINET controller	Yes

Dimensions

Width	15 mm
Height	73 mm
Depth	58 mm

Weights

Weight, approx.	30 g
-----------------	------

Classifications

	Version	Classification
eClass	16	27-24-26-08
eClass	14	27-24-26-08
eClass	12	27-24-26-08
eClass	9.1	27-24-26-08
eClass	9	27-24-26-08
eClass	8	27-24-26-08
eClass	7.1	27-24-26-08
eClass	6	27-24-26-08
ETIM	10	EC001604
ETIM	9	EC001604
ETIM	8	EC001604
ETIM	7	EC001604
IDEA	4	3564
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval	EMV	Maritime application
--------------------------	-----	----------------------

[Miscellaneous](#)

[Manufacturer Declaration](#)



[China RoHS](#)



Environment

[China RoHS](#)

last modified:

4/21/2026