

Siemens
EcoTech



SIMATIC ET 200SP, BaseUnit BU15-P16+A0+2D/T, BU type A1, Push-in terminals, without AUX terminals, New load group, WxH: 15x 117 mm, with temperature acquisition



General information	
Product type designation	BU type A1
HW functional status	FS10 and higher
Supply voltage	
Rated value (DC)	24 V
external protection for power supply lines	Yes; 24 V DC/10 A miniature circuit breaker with type B or C tripping characteristic
Current carrying capacity	
For P1 and P2 bus, max.	10 A
For process terminals, max.	2 A
Hardware configuration	
Temperature sensor	Yes
Formation of potential groups	
• New potential group	Yes
• Potential group continued from the left	No
Slots	
• Number of slots	1; Type A1
Potential separation	
between the potential groups	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	0.873 kg
— global warming potential, (during production) [CO2 eq]	0.866 kg
— global warming potential, (during operation) [CO2 eq]	0 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.0011 kg
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C

• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Absolute humidity	
• dew point, min.	-60 °C; suitable for dry room applications

Accessories

Color coding labels	
• for process terminals	CC00 to CC09
• for AUX terminals	does not exist
• for add-on terminals	does not exist

Connection method

Terminals	
• Terminal type	Push-in terminal
• system-integrated shield connection	Yes; Optional
• Conductor cross-section, min.	0.14 mm²; AWG 26
• Conductor cross-section, max.	2.5 mm²; AWG 14
• Number of process terminals to I/O module	16
• Number of terminals to AUX bus	0
• Number of add-on terminals	0
• Number of terminals with connection to P1 and P2 bus	2

Dimensions

Width	15 mm
Height	117 mm
Depth	35 mm

Weights

Weight, approx.	40 g
-----------------	------

Classifications

	Version	Classification
eClass	16	27-24-26-03
eClass	14	27-24-26-03
eClass	12	27-24-26-03
eClass	9.1	27-24-26-03
eClass	9	27-24-26-03
eClass	8	27-24-26-03
eClass	7.1	27-24-26-03
eClass	6	27-24-26-03
ETIM	10	EC001598
ETIM	9	EC001598
ETIM	8	EC001598
ETIM	7	EC001598
IDEA	4	3560
UNSPSC	15	32-15-17-04

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)



General Product Approval



[CCC-Ex](#)

[FM](#)

For use in hazardous locations	Maritime application
--------------------------------	----------------------



IECEEx



ATEX

[Type Examination Certificate](#)

[Miscellaneous](#)

[CCC-Ex](#)



ABS

Maritime application



DNV



LRS

[NK / Nippon Kaiji Kyokai](#)



RINA



RMRS

Maritime application	Environment
----------------------	-------------

[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)



Siemens
EcoTech



last modified:

2/1/2026