

Siemens
EcoTech



SIMATIC ET 200SP, BaseUnit BU15-P16+A10+2B, BU type A0, Push-in terminals, with 10 AUX terminals, bridged to the left, WxH: 15 mmx141 mm



General information	
Product type designation	BU type A0
HW functional status	From FS06
Supply voltage	
Rated value (DC)	24 V
external protection for power supply lines	Yes; 24 V DC/10 A miniature circuit breaker with type B or C tripping characteristic
Current carrying capacity	
For P1 and P2 bus, max.	10 A
For AUX bus, max.	10 A
For process terminals, max.	2 A
Hardware configuration	
Formation of potential groups	
• New potential group	No
• Potential group continued from the left	Yes
Slots	
• Number of slots	1; Type A0
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	1.09 kg
— global warming potential, (during production) [CO2 eq]	1.08 kg
— global warming potential, (during operation) [CO2 eq]	0 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.0045 kg
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	

• Installation altitude above sea level, max.		5 000 m; Restrictions for installation altitudes > 2 000 m, see manual			
Absolute humidity					
• dew point, min.		-60 °C; suitable for dry room applications			
Accessories					
Color coding labels					
• for process terminals		CC00 to CC09			
• for AUX terminals		CC71 to CC73			
• for add-on terminals		does not exist			
Connection method					
Terminals					
• Terminal type		Push-in terminal			
• system-integrated shield connection		Yes; Optional			
• Conductor cross-section, min.		0.14 mm²; AWG 26			
• Conductor cross-section, max.		2.5 mm²; AWG 14			
• Number of process terminals to I/O module		16			
• Number of terminals to AUX bus		10			
• Number of add-on terminals		0			
• Number of terminals with connection to P1 and P2 bus		2			
Dimensions					
Width		15 mm			
Height		141 mm			
Depth		35 mm			
Weights					
Weight, approx.		50 g			
Classifications					
		Version	Classification		
	eClass	16	27-24-26-03		
	eClass	14	27-24-26-03		
	eClass	12	27-24-26-03		
	eClass	9.1	27-24-26-03		
	eClass	9	27-24-26-03		
	eClass	8	27-24-26-03		
	eClass	7.1	27-24-26-03		
	eClass	6	27-24-26-03		
	ETIM	10	EC001598		
	ETIM	9	EC001598		
	ETIM	8	EC001598		
	ETIM	7	EC001598		
	IDEA	4	3560		
	UNSPSC	15	32-15-17-04		
Approvals / Certificates					
General Product Approval					
		Manufacturer Declaration			
General Product Approval		For use in hazardous locations			
			CCC-Ex	FM	
For use in hazardous locations			Maritime application		

[Type Examination Certificate](#)



[Miscellaneous](#)

[CCC-Ex](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

Maritime application

Environment

[KR \(Korean Register of Shipping\)](#)



last modified:

2/1/2026 