

Siemens
EcoTech



SIMATIC ET 200SP, BaseUnit BU15-P16+A0+12D/T, BU type A1, Push-in terminals, with 2x 5 add-on terminals, New load group, WxH: 15 mm x 141 mm, with temperature acquisition

General information	
Product type designation	BU type A1
HW functional status	FS10 and higher
Supply voltage	
Rated value (DC)	24 V
external protection for power supply lines	Yes; 24 V DC/10 A miniature circuit breaker with type B or C tripping characteristic
Current carrying capacity	
For P1 and P2 bus, max.	10 A
For process terminals, max.	2 A
Hardware configuration	
Additional terminals	Yes
Temperature sensor	Yes
Formation of potential groups	
• New potential group	Yes
• Potential group continued from the left	No
Slots	
• Number of slots	1; Type A1
Potential separation	
between the potential groups	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	1.09 kg
— global warming potential, (during production) [CO2 eq]	1.08 kg
— global warming potential, (during operation) [CO2 eq]	0 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.0045 kg
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C

- vertical installation, min. - vertical installation, max.	-30 °C 50 °C																																													
Altitude during operation relating to sea level																																														
Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual																																													
Absolute humidity																																														
dew point, min.	-60 °C; suitable for dry room applications																																													
Accessories																																														
Color coding labels																																														
- for process terminals - for AUX terminals - for add-on terminals	CC00 to CC09 does not exist CC74																																													
Connection method																																														
Terminals																																														
- Terminal type - system-integrated shield connection - Conductor cross-section, min. - Conductor cross-section, max. - Number of process terminals to I/O module - Number of terminals to AUX bus - Number of add-on terminals - Number of terminals with connection to P1 and P2 bus	Push-in terminal Yes; Optional 0.14 mm²; AWG 26 2.5 mm²; AWG 14 16 0 2x5 2																																													
Dimensions																																														
Width	15 mm																																													
Height	141 mm																																													
Depth	35 mm																																													
Weights																																														
Weight, approx.	50 g																																													
Classifications																																														
	<table><tr><td></td><td>Version</td><td>Classification</td></tr><tr><td>eClass</td><td>16</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>14</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>12</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>9.1</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>9</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>8</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>7.1</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>6</td><td>27-24-26-03</td></tr><tr><td>ETIM</td><td>10</td><td>EC001598</td></tr><tr><td>ETIM</td><td>9</td><td>EC001598</td></tr><tr><td>ETIM</td><td>8</td><td>EC001598</td></tr><tr><td>ETIM</td><td>7</td><td>EC001598</td></tr><tr><td>IDEA</td><td>4</td><td>3560</td></tr><tr><td>UNSPSC</td><td>15</td><td>32-15-17-04</td></tr></table>		Version	Classification	eClass	16	27-24-26-03	eClass	14	27-24-26-03	eClass	12	27-24-26-03	eClass	9.1	27-24-26-03	eClass	9	27-24-26-03	eClass	8	27-24-26-03	eClass	7.1	27-24-26-03	eClass	6	27-24-26-03	ETIM	10	EC001598	ETIM	9	EC001598	ETIM	8	EC001598	ETIM	7	EC001598	IDEA	4	3560	UNSPSC	15	32-15-17-04
	Version	Classification																																												
eClass	16	27-24-26-03																																												
eClass	14	27-24-26-03																																												
eClass	12	27-24-26-03																																												
eClass	9.1	27-24-26-03																																												
eClass	9	27-24-26-03																																												
eClass	8	27-24-26-03																																												
eClass	7.1	27-24-26-03																																												
eClass	6	27-24-26-03																																												
ETIM	10	EC001598																																												
ETIM	9	EC001598																																												
ETIM	8	EC001598																																												
ETIM	7	EC001598																																												
IDEA	4	3560																																												
UNSPSC	15	32-15-17-04																																												
Approvals / Certificates																																														
General Product Approval																																														
 EG-Konf.  Manufacturer Declaration  UL   RCM																																														
General Product Approval	For use in hazardous locations																																													



[FM](#)

[CCC-Ex](#)



For use in hazardous locations



[Type Examination Certificate](#)

[Miscellaneous](#)

[CCC-Ex](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

Maritime application

Environment

[KR \(Korean Register of Shipping\)](#)



Siemens
EcoTech



last modified:

2/1/2026