

product type designation



Cloud Connect CC712

SIMATIC CloudConnect 7, CC712 IoT Gateway for connection of programmable controllers to cloud services and OPC 2xEthernet RJ45 field protocols: S7, S7-Plus, OPC UA, Modbus MES/cloud protocols: MQTT, HTTP, OPC UA

product brand name

SIMATIC NET

Technical Product Detail Page

<https://l.siemens.com/1P6GK1411-1AC00>

transfer rate

transfer rate

- | | |
|------------------------|--------------------|
| • at the 1st interface | 10 ... 1000 Mbit/s |
| • at the 2nd interface | 10 ... 1000 Mbit/s |

interfaces

number of electrical connections

- | | |
|---|---|
| • at the 1st interface / according to Industrial Ethernet | 1 |
| • at the 2nd interface / according to Industrial Ethernet | 1 |
| • for power supply | 2 |

type of electrical connection

- | | |
|---|-----------|
| • at the 1st interface / according to Industrial Ethernet | RJ45 port |
| • at the 2nd interface / according to Industrial Ethernet | RJ45 port |

type of electrical connection

- | | |
|--------------------|----------------------|
| • for power supply | 5-pin terminal strip |
|--------------------|----------------------|

design of the removable storage

- | | |
|-------|-----|
| • CLP | Yes |
|-------|-----|

supply voltage, current consumption, power loss

type of voltage / of the supply voltage

DC

supply voltage

24 V

supply voltage / external

10.8 ... 28.8 V

supply voltage / external / at DC / rated value

24 V

consumed current

- | | |
|---|--------|
| • from external supply voltage / at 24 V DC | |
| — in communication mode / typical | 180 mA |

power loss [W]

4.3 W

ambient conditions

ambient temperature

- | | |
|--|----------------|
| • for vertical installation / during operation | 0 ... 40 °C |
| • for horizontally arranged busbars / during operation | 0 ... 60 °C |
| • during storage | -40 ... +40 °C |
| • during transport | -40 ... +70 °C |

relative humidity

- | | |
|--|------|
| • at 25 °C / without condensation / during operation / maximum | 95 % |
|--|------|

protection class IP

IP20

design, dimensions and weights

module format	Compact
width	35 mm
height	147 mm
depth	127 mm
net weight	0.3 kg
fastening method	
• 35 mm DIN-rail mounting	Yes
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	Yes
• wall mounting	Yes
product functions / cloud connectivity	
protocol / is supported	
• Message Queuing Telemetry Transport (MQTT)	Yes
• Advanced Message Queuing Protocol (AMQP)	No
• HTTP	Yes
• REST-API	Yes
product function / for cloud connectivity	
• trigger management	Yes
• time stamping	Yes
product feature / for cloud connectivity / buffered message frame memory	Yes
number of active connections / for cloud connectivity	3
number of lower-level devices / maximum	1
number of data points per device / maximum	500
performance data / S7 communication	
number of possible connections / for S7 communication	
• maximum	1
performance data / as OPC UA server	
protocol / is supported / OPC UA Server	Yes
number of possible connections / to OPC UA clients / maximum	10
number of variables (items) / maximum	1500
performance data / as OPC UA client	
protocol / is supported / OPC UA Client	Yes
number of possible connections / for OPC UA server / maximum	1
product functions / diagnostics	
product function / web-based diagnostics	Yes
product functions / security	
operating mode / Virtual Private Network (VPN)	No
product function	
• password protection for Web applications	Yes
• SysLog	Yes
product functions / time	
protocol / is supported	
• NTP	Yes
• NTP (secure)	Yes
time synchronization	
• from NTP-server	Yes
• manual setting	Yes
standards, specifications, approvals	
certificate of suitability / CE marking	Yes
certificate of suitability / UKCA marking	Yes
certificate of suitability / cULus approval	Yes
certificate of suitability / KC approval	Yes
certificate of suitability / Regulatory Compliance Mark (RCM)	Yes
certificate of suitability / RoHS conformity	Yes
certificate of suitability / EAC approval	Yes
standards, specifications, approvals / hazardous environments / header	
certificate of suitability / ATEX	Yes
certificate of suitability / IECEx	Yes

certificate of suitability / ULhazloc approval	Yes
certificate of suitability / CCC / for hazardous zone according to GB standard	Yes
certificate of suitability / FM registration	Yes

further information / internet links

internet link	
- to website: Selection guide for cables and connectors - to web page: selection aid TIA Selection Tool - to website: Industrial communication - to web page: SiePortal - to website: Image database - to website: CAX-Download-Manager - to website: Industry Online Support	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/simatic-net https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://siemens.com/cax https://support.industry.siemens.com

security information

security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)
----------------------	--

Approvals / Certificates

General Product Approval



[China RoHS](#)

General Product Approval

EMV

For use in hazardous locations



[FM](#)

For use in hazardous locations

[CCC-Ex](#)

last modified:

6/28/2026