

product type designation



W761-1 RJ45

IWLAN access point, SCALANCE W761-1 RJ45, 1 radio, 1 R-SMA antenna port, IEEE 802.11a/b/g/h/n, 2.4/5 GHz, gross data rate 150 Mbps, 1x RJ45 max. 100 Mbps, 24 V DC, joint block, IP20, 0... +55 °C, WPA2/802.11i/e, observe national approvals! CERT ID: ELN-W1-RJ-E1, scope of supply: manuals on CD-ROM German/English, 1x joint block; for operation outside of USA/Israel ..

product brand name

SCALANCE

Technical Product Detail Page

<https://l.siemens.com/1P6GK5761-1FC00-0AA0>

transfer rate

transfer rate

- | | |
|---------------------------|----------------|
| • with WLAN / maximum | 150 Mbit/s |
| • for Industrial Ethernet | 10, 100 Mbit/s |

interfaces

number of electrical connections

- | | |
|--|---|
| • for network components or terminal equipment | 1 |
| • for power supply | 1 |
| • for redundant voltage supply | 0 |

type of electrical connection

- | | |
|--|-----------------------|
| • for network components or terminal equipment | RJ45 socket |
| • for power supply | 3-pole screw terminal |

memory

design of the removable storage

- | | |
|------------|----|
| • C-PLUG | No |
| • KEY-PLUG | No |

interfaces / wireless

number of radio cards / permanently installed

1

number of electrical connections / for external antenna(s)

1

type of electrical connection / for external antenna(s)

R-SMA (socket)

product feature / external antenna can be mounted directly on device

Yes

supply voltage, current consumption, power loss

type of voltage / of the supply voltage

DC

consumed current

- | | |
|-----------------------------|--------|
| • at DC / at 24 V / typical | 0.15 A |
|-----------------------------|--------|

power loss [W]

- | | |
|-----------------------------|-------|
| • at DC / at 24 V / typical | 3.6 W |
|-----------------------------|-------|

supply voltage / 1

- | | |
|-----------------------|--------|
| • from terminal block | 19.2 V |
|-----------------------|--------|

supply voltage / 2

- | | |
|-----------------------|--------|
| • from terminal block | 28.8 V |
|-----------------------|--------|

ambient conditions

ambient temperature

- | | |
|--------------------|----------------|
| • during operation | 0 ... 55 °C |
| • during storage | -40 ... +85 °C |

• during transport	-40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
ambient condition / for operation	When used under hazardous conditions (Zone 2), the SCALANCE W761-1 RJ45 or W72x-1 RJ45 product must be installed in an enclosure. To comply with EN 50021, this enclosure must meet the requirements of at least IP 54 in compliance with EN 60529.
protection class IP	IP20
design, dimensions and weights	
width	50 mm
height	114 mm
depth	74 mm
width / of the enclosure / without antenna	50 mm
height / of the enclosure / without antenna	114 mm
depth / of the enclosure / without antenna	74 mm
net weight	0.13 kg
fastening method	
• S7-300 rail mounting	No
• S7-1500 rail mounting	No
• 35 mm DIN-rail mounting	Yes
• wall mounting	No
radio frequencies	
operating frequency	
• for WLAN in 2.4 GHz frequency band	2.41 ... 2.48 GHz; depending on the country approvals
• for WLAN in 5 GHz frequency band	4.9 ... 5.8 GHz; depending on the country approvals
product features, product functions, product components / general	
product function / Access Point Mode	Yes
product function / client Mode	Yes
number of SSIDs	1
product function	
• iPCF Access Point	No
• iPCF client	No
• iPCF-MC Access Point	No
• iPCF-MC client	No
product function / iREF	No
product function / iPRP	No
product functions / management, configuration, engineering	
number of manageable IP addresses / in client	4
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• configuration with STEP 7 in the TIA Portal	Yes
• operation with IWLAN controller	No
• operation with Enterasys WLAN controller	No
• forced roaming on IP down with IWLAN	Yes
• forced roaming on link down with IWLAN	Yes
• WDS	Yes
protocol / is supported	
• Address Resolution Protocol (ARP)	Yes
• ICMP	Yes
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• DCP	Yes
• LLDP	Yes
identification & maintenance function	

• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
product functions / diagnostics	
product function	
• PROFINET IO diagnosis	No
• link check	No
• connection monitoring IP-Alive	No
• localization via Aeroscout	No
• SysLog	Yes
protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
product functions / VLAN	
product function	
• function VLAN with IWLAN	Yes
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP server	Yes
• DHCP Option 82	Yes
product functions / redundancy	
protocol / is supported	
• STP/RSTP	Yes
• MSTP	Yes
• RSTP	Yes
product functions / security	
product function	
• ACL - MAC-based	Yes
• management security, ACL-IP based	Yes
• IEEE 802.1x (radius)	Yes
• NAT/NAPT	Yes
• access protection according to IEEE802.11i	Yes
• WPA/WPA2	Yes
• TKIP/AES	Yes
protocol / is supported	
• SSH	Yes
• RADIUS	Yes
product functions / time	
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• SIMATIC time synchronization (SIMATIC Time)	Yes
standards, specifications, approvals	
standard	
• for FM	FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4, FM16US0205X
• for safety / from CSA and UL	UL 60950-1 E115352, CSA C22.2 No. 60950-1
certificate of suitability	
• EC Declaration of Conformity	Yes
• CE marking	Yes
• C-Tick	Yes
• E1 approval	No
• railway application in accordance with EN 50155	No
• railway application in accordance with EN 50121-4	No
• NEMA TS2	No
• IEC 61375	No
• IEC 61850-3	No

• NEMA4X • Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af • Power-over-Ethernet according to IEEE802.3at for type 2	No
	No
	No
standard for wireless communication	
• IEEE 802.11a • IEEE 802.11b • IEEE 802.11e • IEEE 802.11g • IEEE 802.11h • IEEE 802.11i • IEEE 802.11n	Yes
	Yes
	Yes
	Yes
	Yes
	Yes
	Yes
wireless approval	You will find the current list of countries at: www.siemens.de/funkzulassungen
standards, specifications, approvals / marine classification	
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • DNV GL • Korean Register of Shipping (KRS) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS) • Royal Institution of Naval Architects (RINA)	No
	No
	No
	No
	No
	No
	No
	No
standards, specifications, approvals / hazardous environments	
standard / for hazardous zone	EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• from CSA and UL	ANSI/ISA 12.12.01-2013, CAN/CSA C22.2 No.213-M1987, Cl. 1, div. 2, GP. A, B, C, D, T4 / Cl. 1, Zone 2, GP IIC E240480
certificate of suitability / CCC / for hazardous zone according to GB standard	Yes; GB3836.1, GB3836.8
• as marking	Ex nA IIC T4 Gc
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total • during manufacturing • during operation • after end of life	125.8 kg
	12.97 kg
	112.66 kg
	0.17 kg
accessories	
accessories	24 V DC screw terminal included in scope of delivery
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to web page: WLAN country approval • to the website: IWLAN • to website: Industrial communication • to web page: SiePortal • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/wireless-approvals https://www.siemens.com/iwlan https://www.siemens.com/simatic-net https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial

cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval



[Declaration of Con-
formity](#)



[China RoHS](#)

[Manufacturer Declara-
tion](#)

[Type Examination Cer-
tificate](#)

General Product Approval

For use in hazardous locations

[TUEV](#)

[China RoHS](#)



For use in hazard-
ous locations

Radio Equipment Type Approval Certificate

[CCC-Ex](#)

[Miscellaneous](#)

SUBTEL

[Miscellaneous](#)

[Miscellaneous](#)

[Miscellaneous](#)

Environment



last modified:

3/10/2026